

44M SERIES

SMALL BUT POWERFUL

**GENERAL SPECIFICATIONS**

Step Angle	3.6°
Step Accuracy	± 0.4°
Operating Temperature	100°C Max
Ambient Temperature Range	-20°C ~ +70°C
Insulation Resistance at 500Vdc	100MΩ
Dielectric Withstanding Voltage	650 ± 50 VRMS, 2 sec

 [CLICK HERE TO
PRINT THIS SERIES](#)
OPENS PDF IN NEW WINDOW

The specifications in this publication are believed to be accurate and reliable. However, it is the responsibility of the product user to determine the suitability of Portescap products for a specific application. While defective products will be replaced without charge if promptly returned, no liability is assumed beyond such replacement.


Portescap Danaher Motion motors will not be CE marked where the Low Voltage Directive, the Electro-Magnetic Compatibility or other appropriate EU directives are not applicable - this is an EU legal requirement.

TECHNICAL SPECIFICATIONS

	BIPOLAR	
Part Number	44M100D1B	44M100D2B
DC Operating Voltage	5	12
Resistance per Winding (ohms)	12.5	70
Inductance per Winding (mH)	6.7	35
Holding Torque* (mNm/oz-in)	46.6 / 6.6	46.6 / 6.6
Rotor Moment of Inertia (g.m ²)	8.3 x 10 ⁻⁴	8.3 x 10 ⁻⁴
Detent Torque (mNm/oz-in)	8.47 / 1.20	8.47 / 1.20
Step Angle	3.6°	3.6°
Step Angle Tolerance*	± 0.4°	± 0.4°
Steps per Revolution*	100	100
Max. Operating Temperature	100°C	100°C
Ambient Temperature Range		
Operating	-20°C to 70°C	-20°C to 70°C
Storage	-40°C to 85°C	-40°C to 85°C
Bearing Type	Sintered bronze sleeve	Sintered bronze sleeve
Insulation Resistance at 500Vdc	100 megohms	100 megohms
Dielectric Withstanding Voltage	650 ± 50 VRMS, 2 sec	650 ± 50 VRMS, 2 sec
Weight (g/oz)	88 / 3.1	88 / 3.1
Leadwires	28 AWG, UL Style 3265	28 AWG, UL Style 3265

* Measured with 2 phases energized

WIRING DIAGRAM





BIPOLAR


CW ROTATION ↓	STEP	01-04	02-03	05-08	06-07	↑ CCW ROTATION
	1	ON	OFF	ON	OFF	
	2	ON	OFF	OFF	ON	
	3	OFF	ON	OFF	ON	
	4	OFF	ON	ON	OFF	
	1	ON	OFF	ON	OFF	

MOTOR DYNAMICS

CLICK ON A THUMBNAIL TO MAGNIFY

44M100D1B, Bipolar,
L/R Drive44M100D2B, Bipolar,
L/R Drive44M100D1B, Bipolar,
Chopper Drive


MOTOR DYNAMICS

[CHART INDEX](#)

MOTOR DYNAMICS



CHART INDEX



MOTOR DYNAMICS



CHART INDEX

TORQUE VS SPEED

BIPOLAR 44MI00DIB CHOPPER DRIVE
@ 36V, 400mA/Ø, 2Ø

