





REV.	DATE	DESCRIPTION
NC	03/06/00	INITIAL RELEASE
A	12/15/05	UPDATE DRAWING FORMAT



CRIMP NOTES:

1. CRIMPED FERRULE
HEX CRIMP SIZE .255"

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex			
8						DRAWN	G.R.S.	12/15/05					
7						CHECKED			PART DESCRIPTION BULKHEAD CABLE TERMINATION (FOR RG–59/U, LMR240 CABLE)				
6						ISSUED							
5	FERRULE	COPPER	NICKEL	1		SHEET	1 OF 1						
4	HEX NUT	BRASS	NICKEL	1			PART NO.		142273				
3	LOCK WASHER	BRASS	NICKEL	1									
2	INSULATOR	TEFLON	NATURAL	1			DWG. NO.		142273.DWG				
1	BODY	BRASS	NICKEL	1			REV. A						SIZE A
	DESCRIPTION	MATERIAL	FINISH	QTY			C:/142/142273.DWG						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[142273](#)