



Coax Probes

DOUBLE ENDED


SIGNAL PLUNGERS



100546



100547



PROBE SPECIFICATIONS

Minimum Centers: .100 (2.54)
 Current Rating: 0.5 amps continuous
 Spring Force:
 Signal Conductor:
 1.1 oz. @ .023 (0.58) travel, each end
 Shielding Plunger:
 2.2 oz. @ .023 (0.58) travel, each end
 Nominal Impedance: 50 Ω
 Maximum Travel: .050 (1.27), each end
 Working Travel: .023 (0.58), each end

MATERIALS

Barrel: Brass, gold plated
 Spring:
 Signal Conductor: Music wire, gold plated
 Shielding Plunger: Music wire, gold plated
 Shielding Plunger: Copper alloy, gold plated
 Isolation Plug: Torlon
 Dielectric Insulator: Air
 Shielding Tube: Stainless steel, gold plated
 Signal Conductor: Special Quad-0 probe

PROBE SPECIFICATIONS

Minimum Centers: .070 (1.78)
 Current Rating: 0.5 amps continuous
 Spring Force:
 Signal Conductor:
 1.1 oz. @ .023 (0.58) travel, each end
 Nominal Impedance: 50 Ω
 Maximum Travel: .050 (1.27), each end
 Working Travel: .023 (0.58), each end

MATERIALS

Spring: Music wire, gold plated
 Isolation Plug: Torlon
 Dielectric Insulator: Air
 Shielding Tube: Stainless steel, gold plated
 Signal Conductor: Special Quad-0 probe

HOW TO ORDER

100546

B

B

F

BASE PART
NUMBER

TOP
SIGNAL
PROBE
TIP

BOTTOM
SIGNAL
PROBE TIP

MOUNTING
FLANGE

HOW TO ORDER

100547

B

B

BASE PART
NUMBER

TOP
SIGNAL
PROBE
TIP

BOTTOM
SIGNAL
PROBE TIP

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

IDI:

100547-B-C