




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	G	REV PER OG3A-0176-02	08APR02	JR	TM
	G1	REVISED PER ECO-17-002887	31AUG2017	RS	DR



- 1 INSULATION $\varnothing$ 4.318[$\varnothing$.170] MAX.
- 2 FITS TAB 0.406[.016] THK.

AMP INCORPORATED CUSTOMER SERVICE SYSTEM		MAX RECOMMENDED OPERATING TEMPERATURE: —	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L OLMEDA 13NOV95	 TE Connectivity				
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752		DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± 0.25[.015] 3 PLC ± 0.127[.005] 4 PLC ± — ± — ANGLES	DWN M ELLIS 15NOV95					
		APVD B BARE 15NOV95			NAME RECEPTACLE, 110 SERIES, FASTON™, PIDG™, WIRE SIZE, 16-14 AWG					
									PRODUCT SPEC —	
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	VOLTAGE RATING: — —		APPLICATION SPEC 114-1002	SIZE	CAGE CODE	DRAWING NO		RESTRICTED TO	
FOR ORDER ENTRY	1-800-526-5142			CIRCULAR MIL AREA: — —	MATERIAL BODY,BRASS .016 SLV, NYLON, COLOR, BLUER	FINISH BODY,PRE-TIN	WEIGHT —	A3	00779	C=640927
		CUSTOMER DRAWING					SCALE NTS			