


P/N	COLOR	LEGENDS [each]	"A" WIDTH +/- .002	MARKER PER CARD	STD. PKG. CARDS QTY.
PCM-0 thru PCM-99	WHITE	'0' thru '99' [eo.]	.25 (6.35)	36	25
PCM-100 thru PCM-202	WHITE	'100' thru '200' [eo.]	.36 (9.15)	25	25
PCM-A thru PCM-Z	WHITE	'A' thru 'Z' [eo.]	.25 (6.35)	36	25
PCM-A1 thru PCM-A4	WHITE	'A1', 'A3', 'A4' [eo.]	.25 (6.35)	36	25
PCM-B1 thru PCM-B5	WHITE	'B1', 'B3', 'B4', 'B5', [eo.]	.25 (6.35)	36	25
PCM-C1 thru PCM-C4	WHITE	'C1', 'C2', 'C3', 'C4' [eo.]	.25 (6.35)	36	25
PCM-E1 thru PCM-E3	WHITE	'E1', 'E2', 'E3', [eo.]	.25 (6.35)	36	25
PCM-F1 thru PCM-F4	WHITE	'F1', 'F2', 'F3', 'F4' [eo.]	.25 (6.35)	36	25
PCM-H1 thru PCM-H5	WHITE	'H1', 'H2', 'H3', 'H4', 'H5', [eo.]	.25 (6.35)	36	25
PCM-L1 thru PCM-L5	WHITE	'L1', 'L2', 'L3', 'L4', 'L5', [eo.]	.25 (6.35)	36	25
PCM-M1, PCM-M2	WHITE	'M1', 'M2', [eo.]	.25 (6.35)	36	25
PCM-P1 thru PCM-P3	WHITE	'P1', 'P2', 'P3', [eo.]	.25 (6.35)	36	25
PCM-R1 thru PCM-R5	WHITE	'R1', 'R2', 'R3', 'R4', 'R5', [eo.]	.25 (6.35)	36	25
PCM-S1 thru PCM-S5	WHITE	'S1', 'S2', 'S3', 'S4', 'S5', [eo.]	.25 (6.35)	36	25
PCM-T1 thru PCM-T9	WHITE	'T1', 'T2', 'T3', 'T4', 'T5', 'T6', 'T7', 'T8', 'T9', [eo.]	.25 (6.35)	36	25

TABLE 2		C		C	
P/N	COLOR	LEGENDS (each)	"A" WIDTH +/- .062	MARKER PER CARD	STD. PKG. CARDS QTY.
PCM-X1 thru PCM-X4	WHITE	'X1', 'X2', 'X3', 'X4' (1 eo.)	.25 (6.35)	36	25
PCM-1L1 thru PCM-1L3	WHITE	'1L1', '1L2', '1L3' (1 eo.)	.36 (9.15)	25	25
PCM-2L1 thru PCM-2L3	WHITE	'2L1', '2L2', '2L3' (1 eo.)	.36 (9.15)	25	25
PCM-3L1 thru PCM-3L3	WHITE	'3L1', '3L2', '3L3' (1 eo.)	.36 (9.15)	25	25
PCM-4L1 thru PCM-4L3	WHITE	'4L1', '4L2', '4L3' (1 eo.)	.36 (9.15)	25	25
PCM-1T1 thru PCM-1T3	WHITE	'1T1', '1T2', '1T3' (1 eo.)	.36 (9.15)	25	25
PCM-3T1 thru PCM-3T3	WHITE	'3T1', '3T2', '3T3' (1 eo.)	.36 (9.15)	25	25

NOTES:
1. MILLIMETER ARE IN [].



										CAD FILENAME/LAYERS		100295CA-DC-C10796/02D				
										PANDUIT CORP. TINLEY PARK, ILLINOIS						
										CUSTOMER DRAWING SOLID NUMBERS AND LETTERS PCM-* WIRE MARKER CARDS						
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .12 (XXX) ± .025 (.XX) ± .062 ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.				
2	8/5/10	RVU		.36 (9.15) WAS .25 (6.35). 2 PLCS. 25 WAS 36.			6109	R			DRAWN BY RVU	MAT'L; GMC54WS		SCALE NTS		
1	6/18/10	RVU		ADD 201, & 202 TO PCM-100 THRU PCM-202.			6068	R			DATE 10/14/09			DRAWING NO. C10796		DWG A
0	10/14/09	RVU		DRAWING RELEASE.			5859	R			CHK'D			SIZE		
REV	DATE	BY	CHK	DESCRIPTION			ECN	- R	CUST	SUP						