

MACOM

UHF Hybrid Junction 5 MHz-1GHz

H-1-4

- Broad Frequency Range
- 0°-180° Hybrid with High Isolation

Guaranteed Specifications *

(From - 55°C to + 85°C)


Frequency Range	5 MHz-1 GHz
Isolation (A-B Ports)	5-300 MHz 50 dB Min 300 MHz-1 GHz 40 dB Min

Operating Characteristics

Impedance	50 Ohms Nominal
A & B Ports	100 Ohms Nominal
C & D Ports	7 Watts Max
Input Power	Linear with Frequency (~45° @ 300 MHz)
Phase Shift (A to C or D)	
Environmental	See Appendix for MIL-STD-883 screening option.

* All specifications apply with 50 ohm source and load impedance.
This product contains elements protected by United States Patent 3,311,650.


Functional Diagram



Ordering Information

Model No.	Package
H-1-4 BNC	Connectorized
H-1-4 N	Connectorized
H-1-4 SMA	Connectorized



C-33



Dimensions in () are in mm.

See Appendix for complete physical dimensions.

Typical Performance



Specifications Subject to Change Without Notice.

MA-COM Inc. 1011 Pawtucket Boulevard, Lowell, MA 01853 USA

Telephone: 800-366-2266

2-248

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[M/A-COM Technology Solutions:](#)

[H-1-4-BNC](#) [H-1-4-N](#) [H-1-4-SMA](#) [H-1-4-TNC](#)