

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [35022-0016](#)
Status: **Active**
Description: 2.50mm Pitch Board-in Crimp Housing, 2.95mm Height, Right Angle and Vertical, 16 Circuits

Documents:
[3D Model](#)
[Drawing \(PDF\)](#)
[Product Specification PS-35021-001 \(PDF\)](#)
[Product Specification PS-35022-003 \(PDF\)](#)
[Packaging Specification PK-35022-001 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR19980
UL E29179

General

Product Family Crimp Housings
Series [35022](#)
Application Signal
Product Name Board-In
UPC 800753232419


Physical

Circuits (maximum) 16
Color - Resin Natural
Flammability 94V-0
Gender Male
Glow-Wire Compliant No
Lock to Mating Part None
Material - Resin Nylon
Net Weight 0.398/g
Number of Rows 1
Packaging Type Bag
Panel Mount No
Pitch - Mating Interface 2.50mm
Stackable No
Temperature Range - Operating -40°C to +105°C

Material Info

Reference - Drawing Numbers

Packaging Specification PK-35022-001
Product Specification PS-35021-001, PS-35022-003, RPS-35022-001
Sales Drawing SD-35022-00**



EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[35022Series](#)

Use With
[35044](#) , [35021](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

35022-0016