




LOC	DIST	ZONE	LTR	REVISIONS	DATE	APPD
G	14					
				REVISED PER 0720-0230-93	2/25/94	DAW



AMP WIRE RANGE	UL E13288 Listed
12-10 AWG STRANDED	12-10 AWG STRANDED
LR7189 Certified	MILITARY P/N AND CLASS
NOT CERTIFIED	NOT APPLICABLE

△ STAMP AMP 12-10* APPROX AS SHOWN



AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 170°C MAX
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: NOT APPLICABLE
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	WIRE CROSS SECTIONAL AREA RANGE: 2.62-6.64mm² [5,180-13,100] CIR MILS STRANDED
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE WITHOUT NOTICE. REVISED PER 0720-0230-93.

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN - - - - - TOLERANCES ON: 2 PLG DEC ± - 3 PLG DEC ± - ANGLES	DR 2-9-93 TA BRINKMAN CHK 2-9-93 DA PATTERSON APPD 2-9-93 DE MILLER APPD 2-9-93 JL NECKLEY PRODUCT SPEC	NAME AMP Incorporated Harrisburg, PA 17125-3608
FINISH TIN PLATE 0.00254 [L.000100] MIN THK PER MIL-T-10727	APPLICATION SPEC	TERMINAL, RING TONGUE, BUDGET
SIZE CAGE CODE 00779	DRAWING NO 31112	
SCALE 10:1	SHEET 1 OF 1	

PART NO

31112

31112