





FCI
Copyright FCI.

PRODUCT NO
10052608-001LF




SCALE 5:1

ORDINARY MATING STATE

rev	ecn no	dr	date
A	S07-0151	KHL	2007-05-03
B	S07-0225	KHL	2007-06-27
C	S08-0410	DGOH	2008-12-18
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com			surface 		tolerance std		projection 		 MM			
			TOLERANCES UNLESS OTHERWISE SPECIFIED					 A4		Scale 3:1		
Dr	SH TAN	2005-01-13	ANGULAR LINEAR		6 MAX		±0.2					
Eng	SH TAN	2005-07-28			6 to 30 MAX		±0.3					
Chr	DENNIS GOH	2008-12-18	0° ±2°		30 TO 120 MAX		±0.5		ECN			
Appr	JOEY NG	2008-12-18	Product family					Spec ref				
			title B+B 1.25P RECEPTACLE				dwg no 10052608			Rev. C		
catalog no				CUSTOMER COPY				sheet 1 of 2				

PRODUCT NO
10052608-001LF



NOTES

1. MATERIAL:
HOUSING: LCP, BLACK, UL94V-0
CONTACT: PHOSPHOR BRONZE
2. FINISH:
1.27-5.00 μ m NICKEL UNDERPLATE OVERALL,
0.10-0.30 μ m GOLD AT CONTACT AREA
0.05-0.20 μ m GOLD AT SOLDER AREA
3. COPLANARITY OF TERMINAL: 0.1 mm MAX.
4. NO REMAINS OF GATING AND REMOVAL OF REMAINS ARE ALLOWED ON HOUSING SURFACES.
5. PRODUCT SPECIFICATION: GS-12-391.
6. PACKAGING SPECIFICATION: GS-14-1088.
7. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
8. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN.
9. THIS PRODUCT COMPLIES WITH:
NICA00001-0451 COMMON SPECIFICATION ON MATERIAL-CAUSED FAILURES
NICA00001-5468
AICA00051-0560 GENERAL SPECIFICATION ON SUBSTANCE CONTROL REQUIREMENTS
LOCA52300-078X CONNECTOR PURCHASE SPECIFICATION

10. A $\triangle$ SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW OR NOTE WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION.



title B+B 1.25P RECEPTACLE

catalog no

dwg no

10052608

Rev.

C

CUSTOMER COPY

sheet 2 of 2