


NOTES:

1. MATERIALS AND FINISHES:
BODY - BRASS, NICKEL PLATING
CONTACT - PHOSPHOR BRONZE, GOLD PLATING
INSULATOR - DELRIN,NATURAL
2. ELECTRICAL:
A. IMPEDANCE: 50 OHM
B. FREQUENCY RANGE: DC 0-4 GHz
C. DIELECTRIC WITHSTANDING VOLTAGE: 1500 VRMS, MIN.
3. MECHANICAL:
A. DURABILITY: 500 CYCLES MIN.
B. TEMPERATURE RANGE: - 40°C to +80°C
4. CRIMPED FERRULE
HEX CRIMP SIZE .178"
5. CRIMPED CONTACT PIN
HEX CRIMP SIZE .068"


THIRD ANGLE PROJ.

REVISIONS





REV	DESCRIPTION	DATE	ECO	APPR
B	REDRAWN TO UPDATE FORMAT	26-Mar-08	47078	Angela
C	REDRAWN IN PRO/E	15-Oct-13	49746	RM



RECOMMENDED
CABLE STRIPPING DIM'S
SCALE 5.000



SCALE 2.000



CUSTOMER OUTLINE DRAWING
ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE: <0.5mm ± 0.05mm 0.5 - 6mm ± 0.1mm 6 - 30mm ± 0.2mm 30 - 120mm ± 0.3mm ANGLES ± 1° NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. the furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.	MATERIAL -		DRAWN R. MAO	DATE 08-Oct-13	TITLE BNC R/A CRIMP PLUG FOR RG-316/U CABLE		Amphenol RF www.amphenolrf.com	
	REFERENCE AND CONFIGURATION LEVEL:		ENGINEER S. LI	DATE 08-Oct-13			DRAWING NO. B1122E1-ND3G-316U-50	
	FINISH		APPROVED S. HSIEH	DATE 15-Oct-13	SCALE: 3.0:1.0 SHEET 2 OF 2		ITEM NO. 011122AAH36ND5F	
			CAD FILE		DWG SIZE B		REV C	
							PART NO. 031-5991-RFX	