

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
FT	0		1	-	10DEC2008	SS	CR

D

D

C





C

B

B

A

A



RECOMMENDED PC BOARD LAYOUT

1. MATERIALS:
HOUSING: PA 6-6, UL 94V-0, COLOR: DK GRAY
TERMINAL: PHOSPHOR BRZ, TIN PLATED
2. SUITABLE FOR 1.6-2.4mm PC BOARD THICKNESS.
3. RECOGNIZED UNDER THE COMPONENT PROGRAM OF UNDERWRITERS LABORATORIES INC. FILE NO. E60677.
4. IMQ CERTIFICATE WITH SURVEILLANCE ON CONFORMITY WITH IEC 998-1/998-2-1.
5. NOT CUMULATIVE TOLERANCE.
6. TE LOGO TO APPEAR ON HOUSING, LOCATION OPTIONAL WHERE SPACE PERMITS.
7. STANDARD PACKAGE.
8. TAPE AND REEL PACKAGE.

THIS PRINT IS
PRELIMINARY
THE INFORMATION CONTAINED IN THIS DOCUMENT
IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS
DO NOT REPRODUCE OR DISTRIBUTE
DESIGN IS SUBJECT TO CHANGE WITHOUT NOTICE

8	20.32	25.40	3	2-1986486-3
7	20.32	25.40	3	1986486-3
NOTES	DIM B	DIM A	NO OF POS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN S. SCHLEGEL	10DEC2008	Tyco Electronics Harrisburg, PA 17105-3608	
DIMENSIONS: mm		CHK C. RICHARD	10DEC2008	NAME C. RICHARD	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ±0.3 2 PLC ±0.25 3 PLC ±0.000 4 PLC ±0.000 ANGLES ±2° FINISH		APVD C. RICHARD	10DEC2008		
MATERIAL		PRODUCT SPEC -	APPLICATION SPEC -	WEIGHT -	RESTRICTED TO -
1		CUSTOMER DRAWING		SCALE 4:1	SHEET OF REV