









Copyright FCI.



CONFIDENTIAL

rev	ecn no	dr	date
E	S20062	JPEH	2002/06/06
F	S04-0172	JPEH	2004/08/11
G	S04-0224	KBM	2004/10/25
H	S05-0060	KBM	2005/02/28
J	S06-0236	KHL	2006/07/17
K	S10-0205	PR	2009/12/17
-	-	-	-

www.fciconnect.com			surface -  ISO 1302		tolerance std ISO 406 ISO 1101		projection 		MM 						
			TOLERANCES UNLESS OTHERWISE SPECIFIED												
Dr	JPEH	2002/06/06	ANGULAR	LINEAR	0.X	±-	size A3	Scale 10:1							
Eng	JPEH	2004/08/11			0.XX	±0.25									
Chr	KH LEE	2009/12/17	0°	±3°	0.XXX	±-	ECN		S10-0205						
Appr	JOEY NG	2009/12/17	Product family				MINITEK	Spec ref -							
		title				POL. MINITEK II				dwg no		61698		Rev.	
						SMT STR HEADER (DUPLEX)								K	
		catalog no				-				CUSTOMER		sheet 1 of 2			

REV F - 2006-04-17



Copyright FCI.

A

B

C

D

PRODUCT NO. SEE NOTE 8	POS	POL. POS	DIM X	DIM Y
61698-X01	2X22	20	42	44
-X02	2X13	1	24	26
-X03	2X16	3,4,5,6,32	30	32

NOTES:

- MATERIAL:
BODY : HIGH TEMPERATURE THERMOPLASTIC UL 94V-0 BLACK
PIN : COPPER ALLOY
- TOLERANCE UNLESS OTHERWISE NOTED ± 0.25
- DIM 1.0 APPLIES TO MOLDED SIDE(S) ONLY.
IF SIDE(S) ARE BROKEN, DIM 1.5 MAX APPLIES.
- RECESS APPLIES TO MOLDED SIDE(S) ONLY.
- PLATING ON MATING LENGTH:
-3XX --- 0.38 μ m Au OVER 1.27 μ m MIN NICKEL UNDERPLATE.
-5XX --- 0.38 μ m PdNi W Au FLASH OVER 1.27 μ m MIN NICKEL UNDERPLATE.
-6XX --- 0.76 μ m PdNi W Au FLASH OVER 1.27 μ m MIN NICKEL UNDERPLATE.
- SOLDER TAIL PLATING:
a) SOLDER TAIL OF P/N:61698-XXX IS 3.81 μ m MIN TIN/LEAD (90/10) PLATED OVER 1.27 μ m MIN NICKEL UNDERPLATE.
b) SOLDER TAIL OF P/N:61698-XXXLF IS 2.54 μ m MIN 100% MATTE TIN PLATED OVER 1.27 μ m MIN NICKEL UNDERPLATE (LEADFREE).
- PACKAGING:
a) STANDARD PACKAGING IN PLASTIC BAG.
b) SPECIFY 61698-XXXT FOR TUBE PACKAGING.
c) SPECIFY 61698-XXXTR FOR TAP AND REEL PACKAGING.
A PICK-UP CAP IS PROVIDED IN THE CENTRE OF THE PRODUCT (SEE FIG.1) FOR PICK AND PLACE APPLICATION.
d) SPECIFY 61698-XXXTC FOR TUBE PACKAGING WITH PICK-UP CAP IN CENTRE OF PRODUCT(SEE FIG.1).

PICK-UP CAP






FIG. 1
NOTE 7 (c)&(d)
SCALE 5:1

- PART NUMBER INFORMATION
61698-XYZZLF
LEAD FREE. SEE NOTES 6b,12
TYPE OF PACKAGING SEE NOTE 7
DASH NUMBER
PLATING AT MATING. SEE NOTE 5
BASE NUMBER
- COPLANARITY OF SOLDER LEADS TO BE WITHIN 0.10mm.
- POLARISED BY OMISSION OF PINS. REFER TO TABLE FOR POL. POS.
- THE HOUSING WILL WITHSTAND EXPOSURE TO 255°C PEAK TEMPERATURE FOR 10 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN.
- THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- A $\triangle K$ SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW OR NOTE WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION.

CONFIDENTIAL

www.fciconnect.com			surface ISO 1302		- ✓ tolerance std ISO 406 ISO 1101		projection 		MM 			
			TOLERANCES UNLESS		OTHERWISE SPECIFIED							
Dr	JPEH	2002/06/06	ANGULAR		LINEAR		0.X	±-	size A3	Scale 10:1		
Eng	JPEH	2004/08/11					0.XX	±0.25				
Chr	KH LEE	2009/12/17	0°	±3°			0.XXX	±-	ECN	S10-0205		
Appr	JOEY NG	2009/12/17	Product family				MINITEK		Spec ref -			
			title POL. MINITEK II SMT STR HEADER (DUPLEX)				dwg no 61698				Rev. K	
			catalog no -				CUSTOMER				sheet 2 of 2	