



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN	APVD	
	D	Hsg mat change to readily available PBT resin	03JAN2014	PS	JK	

POS. PER ROW 'N'	L	PART NUMBER	
1	-	-	-
2	5.08	-215 311-2	OBSOLETE
3	7.62	-3	OBSOLETE
4	10.16	-4	
5	12.70	-5	
6	15.24	-6	
7	17.78	-7	OBSOLETE
8	20.32	-8	
9	22.86	-9	
10	25.40	1-	-0
11	27.94	1-	-1
12	30.48	1-	-2
13	33.02	1-	-3
14	35.56	1-	-4
15	38.10	1-	-5
16	40.64	1-	-6
17	43.18	1-	-7
18	45.72	1-	-8
19	48.26	1-	-9
20	50.80	2-	-0
21	53.34	2-	-1
22	55.88	2-	-2
23	58.42	2-	-3
24	60.96	2-	-4
25	63.50	2-	-5
26	66.04	2-	-6
27	68.58	2-	-7
28	71.12	2-	-8
29	73.66	2-	-9
30	76.20	3-	-0
31	78.74	3-	-1
32	81.28	3-	-2
33	83.82	3-	-3
34	86.36	3-	-4
35	88.90	3-	-5
36	91.44	3- 215 311-6	OBSOLETE



P.C.-BOARD HOLE-PATTERN


HV 100 CONTACT	Cu Sn	2
HV 100 HOUSING	PBT	GREEN
DESCRIPTION	MATERIAL	FINISH/COLOR

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.15
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -
MATERIAL SEE TABLE	FINISH SEE TABLE

DWN WRULICH 13.12.88				
CHK M.SCHAARSCHMIDT 06.12.90				
APVD -	NAME HV100 CONN. VERTICAL, 7.0mm TOP ENTRY, DUAL ROW, GOLD (SEALED VERSION)			
PRODUCT SPEC 108-19056				
APPLICATION SPEC -				
WEIGHT -	SIZE A3	CAGE CODE 00779	DRAWING NO C-215311	RESTRICTED TO -
CUSTOMER DRAWING			SCALE 5:1	SHEET 1 OF 2
			REV D	

NOTES:


- 1 CONTACT POINT
- 2 PLATING: UNDER COATING: 1,3 μm Ni.
AT CONT.PLACE: 0,8 μm Au.
AT SOLDER-TYNES: 3,0-5,0 μm Sn
3. RECOMMENDED P.C.BOARD-THICKNESS: 1,6mm.
4. MATES WITH 0,63 SQUARE/ROUND MODU POSTS.
- 5 HIGH TEMPERATURE SEALANT
- 6 PC-BOARD RETENTION FEATURE
7. HV100 CONNECTOR PACKED IN ANTI-STATIC BLISTER TRAY
- 8 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI




THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION	
© COPYRIGHT - By -		ALL RIGHTS RESERVED.	
POLZ. PRO REIHE	L +0.3 -0.1	BESTELL-NR.	NICHT VERMASSTE KANTEN SIND NICHT MAßSTÄBLICH
-	-	-	ÄNDERUNGEN DIE DEM TECH- NISCHEN FORTSCHRITT DIENEN, BEHALTEN WIR UNS VOR

LOC	DIST	REVISIONS			
Al	-	P	LTR	DESCRIPTION	DATE
VERWENDET FÜR E 91-52 572		-	-	SEE SHEET 1	-

-	-	-	-
3	7.62	5	215 311 3
4	10.16	5	4
5	12.70	5	5
6	15.24	5	6
7	17.78	5	7
8	20.32	5	8
9	22.86	5	9
10	25.40	6	0
11	27.94	6	1
12	30.48	6	2
13	33.02	6	3
14	35.56	6	4
15	38.10	6	5
16	40.64	6	6
17	43.18	6	7
18	45.72	6	8
19	48.26	6	9
20	50.80	7	215 311 0



- 1 KONTAKTPUNKT
- 2 IM KONTAKTBEREICH $0.8 \mu m$ Au ÜBER $1.3 \mu m$ Ni
IM LÖTBEREICH MIN. $3.0 \mu m$ Sn ÜBER $1.3 \mu m$ Ni
- 3 EMPFOHLENE LEITERPLATTENDICKE 1.6mm
- 4 STECKBAR MIT MODU II STIFTEN $\phi / \square 0.63$
- 5 HOCH TEMPERATURBESTÄNDIGER KLEBER
- 6 FIXIERUNG IN LEITERPLATTE
DURCH BIEGUNG DER KONTAKTENDEN
- 7 HV100 BUCHSENSTECKER VERPACKT IN ANTI-
STATISCHEM BLISTER TRAY
- 8 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER
D.RENAUD/D.SINISI



						ZEICHNUNG GÜLTIG AB KW .06/.96																	
						THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN A.HO 18.09.91		 TE Connectivity											
										CHK M.SCHAARSCHMIDT 28.06.91													
						DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.15				APVD —		NAME									
								0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —				PRODUCT SPEC 108—19056		HV100 CONN. VERTICAL, 7.0mm TOP ENTRY, DUAL ROW, GOLD (SEALED VERSION)									
		APPLICATION SPEC —																					
						MATERIAL		FINISH				WEIGHT —		SIZE A3		CAGE CODE 00779		DRAWING NO C—215311				RESTRICTED TO —	
						SEE TABLE		SEE TABLE				CUSTOMER DRAWING		SCALE 5:1		SHEET 2 OF 2		REV D					

SIEHE TABELLE	2		HV 100 KONTAKT	Cu Sn	
	1	—	HV 100 GEHÄUSE	PBTP GV	GRÜN
BESTELL—NR.	POS.	STÜCK	BENENNUNG EINZELTEIL	WERKSTOFF	OBERFLÄCHE 19.09.91