






PRODUCT NO	TERMINAL BODY		LEAD FREE
	MATERIAL	PLATING OR GOLD DOT	OPTION
65829-001	0.25/.010 THK 1/4 HD CU NI ALLOY UNS C72500	.002/.001 MIN THK GOLD DOT	--- -- OBSOLETE
65829-002	0.25/.010 THK 1/4 HD BRASS ALLOY UNS C26000	1.02 μ /40 μ " GOLD AT CONTACT REMAINDER GOLD FLASH OVER 1.27 μ /50 μ " NICKEL	--- -- OBSOLETE
65829-003	0.25/.010 BRASS ALLOY	.76 μ /30 μ " Au or GXT AT CONTACT OVER 1.27 μ /50 μ " NICKEL	NOTE 5,6



SECTION XX



- NOTES:
- WHITE LINES AS SHOWN FOR POLARIZATION.
 - HOUSING MAT'L: PLAIN POLYESTER, OPT. PLAIN NORYL, FLAME RETARDANT PER UL-94V-0 COLOR BLACK.
 - TERMINAL BODY MAT'L: SEE TABLE
 - SPRING MAT'L: 0.122/.0048 TH'K BE CU ALLOY, UNS C17200. HEAT TREATED PLATING: GOLD FLASH.
 - ADD "LF" SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE OPTION.
 - THESE PRODUCTS MEET EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
 - THE PRODUCT IS NOT INTENDED TO BE EXPOSED TO A MANUFACTURING SOLDER PROCESS.

mat'l. code		surface ISO 1302	tolerance ISO 406 ISO 1101	projection ISO 1101	product family JUMPER
l	tr	ec	n	d	r
E	ADDED	EBY	4/9/86	date	tolerances unless otherwise specified
F	M05-0205	MHT	9/30/05	angles	linear
G	M06-0238	MN	06/16/06	0°±2'	linear
H	M06-0389	AGS	10/4/06	dr	M. HERNANDEZ
J	SLX-H-011384	J.Z	2012-04-24	engr	S. FIERRO
				chr	S. FIERRO
				appd	S. FIERRO
sheet	revision				
index	sheet	1			

FCIconnect.com

Copyright FCI