


CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes




ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	7-8 @20°C	0.165 ohms max.
D.C. RESISTANCE	5-6 @20°C	0.075 ohms max.
D.C. RESISTANCE	2-4 tie(+2, 3+4), @20°C	0.010 ohms max.
INDUCTANCE	5-6 10kHz, 100mVAC, Is	16.9uH ±10%
LEAKAGE INDUCTANCE	5-6 tie(+2+3+4, 7+8), 100kHz, 50mVAC, Is	500mH max.
DIELECTRIC	1-8 tie(3+4, 8+7), 1500VAC, 1 second	-
DIELECTRIC	6-8 500VDC, 1 second	-
TURNS RATIO	(8-5):(4-2), tie(+2, 3+4)	3.200±1, ±3%
TURNS RATIO	(8-5):(7-8)	1.456±1, ±3%



LOT CODE & DATE CODE

DOT LOCATES TERM. #8



REV.	DATE

6A 6/09

Packaging Specifications

Method: Tape & Reel
PKG-0328
www.midcom-inc.com

DRAWING TITLE

TRANSFORMER

Unless otherwise specified:
Tolerances: Fractions: $\pm 1/64$
Angles: $\pm 1^\circ$ Decimals: $\pm .005$ [127]
This drawing is dual dimensioned. Dimensions in brackets are in millimeters.

eSos p/n: 750310854



REVISIONS: SEE SHEET 1

DRAWING NO.

750310854

SCALE ---

SHEET 2 OF 5