


BZT55C- Series



**RoHS
Compliant**



Features:


- Zener voltage range 2 to 75 Volts.
- Mini-MELF package.
- Surface device type mounting.
- Hermetically sealed glass.
- Compression Bonded Construction.
- All external surfaces are corrosion resistant and terminals are readily solderable.
- Matte Tin (Sn) lead finish.
- Blue color band indicates negative polarity.

Maximum Ratings and Electrical Characteristics


Type Number	Symbol	Value	Units
Power Dissipation	P_D	500	mW
Operating and Storage Temperature Range	T_J, T_{STG}	-65 to + 200	°C

Notes : These ratings are limiting values above which the serviceability of the diode may be impaired.


Ratings and Characteristic Curves




Total Power Dissipation vs. Ambient Temperature



Temperature Coefficient of V_z vs. Z-Voltage




Typical Change of Working Voltage under Operating Conditions at $T_{amb}=25^{\circ}\text{C}$




Diode Capacitance vs. Z-Voltage


BZT55C- Series




Typical Change of Working Voltage vs. Junction Temperature




Forward Current vs. Forward Voltage



Z-Current vs. Z-Voltage




Differential Z-Resistance vs. Z-Voltage



Z-Current vs. Z-Voltage

BZT55C- Series



Electrical Characteristics (TA=25°C unless otherwise noted)

Vz at IzT (Volts)		IzT mA	ZzT at IzT Ω Max.	IzK mA	ZzK at IzK Ω	IR at VR μA Max.	VR V	Vz Typical V	Part Number
Vz Min. (V)	Vz Max. (V)								
9.4	10.6	5	15	1	70	0.1	7.5	10	BZT55C10
10.4	11.6	5	20	1	70	0.1	8.2	11	BZT55C11
11.4	12.7	5	20	1	90	0.1	9.1	12	BZT55C12
12.4	14.1	5	26	1	110	0.1	10	13	BZT55C13
13.8	15.6	5	30	1	110	0.1	11	15	BZT55C15
15.3	17.1	5	40	1	170	0.1	12	16	BZT55C16
16.8	19.1	5	50	1	170	0.1	13	18	BZT55C18
18.8	21.1	5	55	1	220	0.1	15	20	BZT55C20
20.8	23.3	5	55	1	220	0.1	16	22	BZT55C22
22.8	25.6	5	80	1	220	0.1	18	24	BZT55C24
25.1	28.9	2	80	1	220	0.1	20	27	BZT55C27
1.88	2.11	5	100	1	600	50	1	2	BZT55C2V0
2.08	2.33	5	100	1	600	50	1	2.2	BZT55C2V2
2.28	2.56	5	85	1	600	50	1	2.4	BZT55C2V4
2.51	2.89	5	85	1	600	10	1	2.7	BZT55C2V7
28	32	2	80	1	220	0.1	22	30	BZT55C30
31	35	2	80	1	220	0.1	24	33	BZT55C33
34	38	2	80	1	220	0.1	27	36	BZT55C36
37	41	2	90	0.5	500	0.1	28	39	BZT55C39
2.8	3.2	5	85	1	600	4	1	3	BZT55C3V0
3.1	3.5	5	85	1	600	2	1	3.3	BZT55C3V3
3.4	3.8	5	85	1	600	2	1	3.6	BZT55C3V6

BZT55C- Series



V _z at I _{zT} (Volts)		I _{zT} mA	Z _{zT} at I _{zT} Ω Max.	I _{zK} mA	Z _{zK} at I _{zK} Ω	I _R at V _R μA Max.	V _R V	V _z Typical V	Part Number
V _z Min. (V)	V _z Max. (V)								
3.7	4.1	5	85	1	600	2	1	3.9	BZT55C3V9
40	46	2	90	0.5	600	0.1	35	43	BZT55C43
44	50	2	110	0.5	700	0.1	35	47	BZT55C47
4.0	4.6	5	75	1	600	2	1	4.3	BZT55C4V3
4.4	5	5	60	1	600	0.5	1	4.7	BZT55C4V7
48	54	2	125	0.5	700	0.1	38	51	BZT55C51
52	60	2	135	0.5	1,000	0.1	42	56	BZT55C56
4.8	5.4	5	35	1	550	0.1	1	5.1	BZT55C5V1
5.2	6.0	5	25	1	450	0.1	1	5.6	BZT55C5V6
58	66	2.5	150	0.5	1,000	0.1	47	62	BZT55C62
64	72	2.5	160	0.5	1,000	0.1	51	68	BZT55C68
5.8	6.6	5	10	1	200	0.1	2	6.2	BZT55C6V2
6.4	7.2	5	8	1	150	0.1	3	6.8	BZT55C6V8
70	80	2.5	170	0.5	1,000	0.1	56	75	BZT55C75
7.0	7.9	5	7	1	50	0.1	5	7.5	BZT55C7V5
7.7	8.7	5	7	1	50	0.1	6.2	8.2	BZT55C8V2
8.5	9.6	5	10	1	50	0.1	6.8	9.1	BZT55C9V1

V_F Forward Voltage = 1V Maximum at I_F = 100mA for all types.

Notes : 1. The type numbers listed have zener voltage min/max limits as shown.

2. The zener impedance is derived from the 60-cycle AC voltage, which results when an AC current having an rms value equal to 10% of the dc zener current (I_{zT} or I_{zK}) is superimposed to I_{zT} or I_{zK}.

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.