





Frame	Aluminum Die-cast	Notes
Impeller	Metal alloy	Date: 050113
Connection *	Lead wires or Terminal	Environmental Protection: IP55
Motor	AC Shaded pole, Impedance protected	Storage Temp: -40C ~ +100C
Bearing System	Dual Ball bearing	Weight: 430g (0.95lbs)
Insulation Resistance	>100MOhm at 500VDC	Available AC voltages by special order: 12, 24, 28, 38, 42, 48, 440, 480, and dual voltage. Dual speed also available. Call for information.
Dielectric Strength	> 60 seconds at 1500VAC	
Operating Temp Range	-30C ~ +80C (non-condensing)	* Specify configuration: TB = Terminal, Ball bearing WB = Wire leads, Ball bearing
Life Expectancy	50000 hours (55C)	



Model No.	Func. Code	Speed (RPM)	Airflow (CFM)	Noise	Volts AC	Voltage Range AC	Watts	Max. Static Pressure ("H ₂ O)	Curves
OA80AP-11-1 *	1855	2750 3200	28 33	35	115	100 ~ 120	15 13	0.15 0.18	2 (50Hz) 1 (60Hz)
OA80AP-11-2 *	1855	2200 2500	23 26	30	115	100 ~ 120	12 10	0.12 0.14	4 (50Hz) 3 (60Hz)
OA80AP-11-3 *	1855	1700 1900	18 21	23	115	100 ~ 120	8 6	0.07 0.08	6 (50Hz) 5 (60Hz)
OA80AP-22-1 *	1855	2750 3200	28 33	35	230	200 ~ 240	15 13	0.15 0.18	2 (50Hz) 1 (60Hz)
OA80AP-22-2 *	1855	2200 2500	23 26	30	230	200 ~ 240	12 10	0.12 0.14	4 (50Hz) 3 (60Hz)
OA80AP-22-3 *	1855	1700 1900	18 21	23	230	200 ~ 240	8 6	0.07 0.08	6 (50Hz) 5 (60Hz)