



CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes



Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

more than you expect




ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	7-1 @20°C	1.329 max.
D.C. RESISTANCE	5-4 @20°C	0.650 max.
INDUCTANCE	7-1 20kHz, 1.0VAC, Ls	700.0uH ±5%
DIELECTRIC	1-4 1800VAC, 1 second	—
TURNS RATIO	(7-1):(5-4)	5.0:1, ±2%

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

REV.	DATE	Packaging Specifications Method: Tray PKG-0816 www.we-online.com/midcom		CONVENTIONAL PLACEMENT
6A	1/13	SEE REVISION SHEET FOR REVISION LEVEL		

Tolerances unless otherwise specified:
Angles: ±1° Decimals: ±.005 [.13]
Fractions: ±1/64 Footprint: ±.001 [.03]
This drawing is dual dimensioned. Dimensions in brackets are in millimeters.

DRAWING TITLE
INDUCTOR
eSos p/n: 750341595



PART NO.
750341595
SPECIFICATION SHEET 1 OF 1