

15 WATT AC-DC CONVERTER

VTM-SB Series




Features

- Compact
- Isolated outputs
- High Performance and Reliability
- Excellent for equipment/din rail applications

Specifications<AC/DC>	Model			
VTM**SB 15WATTS/SINGLE OUTPUT	VTM05SB	VTM12SB	VTM15SB	VTM24SB
Input Characteristic				
Input Voltage	AC200V(DC260V)			
Input Range	AC180-264V(DC220-350V)			
Input Frequency	50/60Hz			
Input Frequency Range	47 -440Hz			
Phase	Single			
Inrush Current	20A(maximum) at rated input/output			
Efficiency [%] (typical) *1	71	71	71	71

EFFICIENCY CURVE




Specifications<AC/DC>	Model			
VTS**SB 10WATTS/SINGLE OUTPUT	VTS05SB	VTS12SB	VTS15SB	VTS24SB
Output Characteristic				
Output Voltage [V]	5	12	15	24
Output Current [A]	2.0	1.0	0.8	0.5
Voltage Adjust Range	+/-5% of Rated Output Voltage(at no load within input range)			
Ripple and Noise [mVp-p](maximum) *2	100	170	200	290
Regulation				
a.Statistic Line Regulation [mV](maximum)	40	96	120	192
b.Statistic Load Regulation [mV](maximum)	45	108	135	216
c.Temperature Coefficient *3	0.03%/°C			
d.Drift[mV](maximum) *4	40	75	90	135
e.Dynamic Load Regulation [mV](typical) *5	150	360	450	720
f.Recovery Time *5	0.5mS(typical)			
Rise up time	200mS(maximum) at 25°C and rated input/output			
Hold up time	22mS(typical)	14mS(typical) at 25°C and rated input/output		
Functions				
Overcurrent Protection	Current Limiting with automatic recovery			
Overvoltage Protection	Zener diode clamping			
Remote Sense	not available			
Remote On/Off	not available			
Environmental				
Operating Temperature	0 to +50°C			
Operating Humidity	85%RH(non-condensing)			
Storage Temperature	-20 to +85°C			
Storage Humidity	30 to 85%RH(non-condensing)			
Withstanding Voltage	Primary-Secondary AC2,500Vfor 1minute			
	Primary-Frame Ground AC2,500V for 1minute			
	Secondary-Frame Ground AC500V for 1minute			
Isolation Resistance	Primary-Secondary-Frame Ground 50MΩ(minimum) by DC500V insulation tester			
Vibration	5-10Hz:10mm double amplitude,10-55Hz:19.6m/s ² ,20minutes' period for 60minutes each along X,Y,Z axes(non-operating)			
Shock	294m/s ²			
Cooling	Convection			
Leakage Current	1.0mA(maximum)			
Line Conduction Noise	Not specified			
Safety	-			
Weight (typical)	180g			
MTBF [H]	950,000			
Switching Frequency[kHz](typical)	42			


ETA-USA

HIGH QUALITY SWITCHING POWER SUPPLIES


ETA-USA Tel: 408-778-2793 Fax: 408-779-2753 e-mail: sales@eta-usa.com

DIMENSION DIAGRAM



VTM-SA/3B

OCP CURVE



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ETA-USA:](#)

[VTM24SB](#)