


DO NOT SCALE

DIMENSIONS IN MM.



WIRE RANGE: 0.2 TO 0.5 mm².
FOR SEALED AND UNSEALED APPLICATIONS, SINGLE WIRES ONLY MUST BE USED.

INSULATION RANGE:
FOR UNSEALED APPLICATIONS, WIRES OF 1.1 TO 1.8 mm INSULATION DIA. MAY BE USED.
FOR SEALED APPLICATIONS, ONLY WIRES OF 1.6 TO 1.8 mm INS. DIA. MAY BE USED WITH SEAL PN.345791-1.

PRE-TINNED		BRASS		345808-1	
FINISH		MATERIAL		PART NUMBER	
CUSTOMER DWG FOR REFERENCE ONLY		© COPYRIGHT 1993 BY AMP OF GREAT BRITAIN LTD. ALL INTERNATIONAL RIGHTS RESERVED. ALL PRODUCTS MAY BE COVERED BY BRITISH AND FOREIGN PATENTS AND/OR PATENTS PENDING.		RELEASED FOR PUBLICATION 01 APR 1993	
		TOLERANCES UNLESS OTHERWISE STATED: DEC ± 0.5 ANGLES ± 1°		DR. R.J.S. 1.4.93 CH. R.R. APP. J.P.	
A RELEASED		EB00-0041-D1 14.02.01		AMP of Great Britain Ltd.	
2 BOX MT. TOL ALTERED		EB00-0344-95 10.10.95		TERMINAL HOUSE STANMORE MDDX.	
1 PRELIM. ISSUE		01.04.93		NAME	
REV MODIFICATION		CHANGE No.		DATE	
		SCALE		LOC	
		SIZE		DWG. No.	
		5 / 1		E A 3	
		C345808		REV	
		A		SHEET	
		1 / 1			