

## BRADY B-717 THERMAL TRANSFER PRINTABLE GLOSSY WHITE STATIC DISSIPATIVE POLYIMIDE LABEL STOCK

TDS No. B-717  
Effective Date: 01/21/2019

### Description:

#### GENERAL

**Print Technology:** Thermal Transfer

**Material Type:** Polyimide

**Finish:** Glossy

**Adhesive:** Static Dissipative Permanent Acrylic

### APPLICATIONS

Printed circuit board and electronic component pre-process labeling

### RECOMMENDED RIBBONS

Brady Series R6000 Halogen Free

### REGULATORY/AGENCY APPROVALS

**UL:** Brady B-717 is a UL Recognized Component to UL969 Labeling and Marking Standard when printed with the Brady Series R6000 Halogen Free ribbon. See UL file MH17154 for specific details. UL information can be accessed on-line at UL.com in the UL Product iQ area.

For information on the Weee-RoHS compliance status for a Brady Product go to one of the following websites:

In Canada: [www.bradycanada.ca/weee-rohs](http://www.bradycanada.ca/weee-rohs)

In Europe: [www.bradyeurope.com/rohs](http://www.bradyeurope.com/rohs)

In Japan: [www.bradycorp.jp/products/labelsuse/rohs](http://www.bradycorp.jp/products/labelsuse/rohs)

All other regions: [www.bradyd.com/weee-rohs](http://www.bradyd.com/weee-rohs)

### SPECIAL FEATURES

B-717 is constructed with a static dissipative adhesive. This product has adhesive surface resistivity values in the recommended range for dissipative ESD packaging materials as defined by ANSI/ESD S541-2008 (between  $10^4$  and  $10^{11}$  ohms).

B-717 in combination with the Series R6000 Halogen Free ribbon meets the requirements of MIL-STD-202G, Method 215K. Preheat can be employed to further enhance print permanence in the case of extreme solvent and/or abrasion exposure. B-717 is designed to withstand multiple cycles of harsh condition washes for printed circuit boards.

### Details:

| PHYSICAL PROPERTIES              | TEST METHODS                                                      | AVERAGE RESULTS                                                            |
|----------------------------------|-------------------------------------------------------------------|----------------------------------------------------------------------------|
| Thickness                        | ASTM D1000<br>-Substrate<br>-Adhesive<br>-Total (excluding liner) | 0.0025 inch (0.063 mm)<br>0.0017 inch (0.043 mm)<br>0.0042 inch (0.106 mm) |
| Adhesion to:<br>-Stainless Steel | ASTM D1000<br>20 minute dwell<br>24 hour dwell                    | 40 oz/in (44 N/100 mm)<br>55 oz/in (61 N/100 mm)                           |
| Tack                             | ASTM D2979<br>Polyken™ Probe Tack<br>0.5 second dwell             | 49 oz (1400 g)                                                             |
| Drop Shear                       | PSTC-7 (except use ½" x 1" sample)                                | >100 hours                                                                 |
| Dielectric Strength              | ASTM D1000                                                        | 12,000 volts total                                                         |
| Adhesive Surface Resistivity     | EOS/ESD STM11.11                                                  | $3.9 \times 10^8$ ohms/sq                                                  |

Performance properties tested on B-717 printed with the Brady Series R6000 Halogen Free thermal transfer ribbon. Printed samples of B-717 were laminated to aluminum and allowed to dwell 24 hours before exposure to the indicated environmental conditions.

| PERFORMANCE PROPERTIES              | TEST METHODS                                                                                                                                                           | AVERAGE RESULTS                                                                                                                                                                                                                              |
|-------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Short Term High Service Temperature | 80 seconds at various Temperatures                                                                                                                                     | No visible effect to label at 572°F (300°C), label discolors slightly at 626°F (330°C) but still functional, at 662°F (350°C) label still functional but moderately discolored and adhesive discolored at label edge; print is still legible |
|                                     | 5 minutes at various Temperatures                                                                                                                                      | No visible effect to label at 500°F (260°C), label discolors slightly at 518°F (270°C), at 572°F (300°C) label moderately discolors and adhesive discolors at label edge. Label remains functional. Print is still legible                   |
|                                     | 2 hours at various Temperatures                                                                                                                                        | No visible effect to label at 338°F (170°C), label discolors slightly at 374°F (190°C), moderately at 428°F (220°C) and severely at 500°F (260°C). Label remains functional. Print is still legible.                                         |
| Long Term High Service Temperature  | 1000 hours at various Temperatures                                                                                                                                     | No visible effect to label at 212°F (100°C), label discolors slightly at 248°F (120°C), moderately at 293°F (145°C). Label remains functional. Print is still legible.                                                                       |
| Low Service Temperature             | 1000 hours at -94°F (-70°C)                                                                                                                                            | No visible effect                                                                                                                                                                                                                            |
| Humidity Resistance                 | 1000 hours at 100°F (37°C)/95% RH                                                                                                                                      | No visible effect                                                                                                                                                                                                                            |
| UV Light Resistance                 | ASTM G155, Cycle 1, Dry<br>1000 hours in Q-Sun Xenon Test Chamber                                                                                                      | Topcoat turns light yellow, label remains functional                                                                                                                                                                                         |
| Weatherability                      | ASTM G155, Cycle 1<br>1000 hours in Xenon Arc Weather-Ometer®                                                                                                          | Slight discoloration                                                                                                                                                                                                                         |
| Salt Fog Resistance                 | ASTM B117<br>1000 hours in 5% salt fog solution chamber                                                                                                                | No visible effect                                                                                                                                                                                                                            |
| Abrasion Resistance                 | Taber Abraser, CS-10 grinding wheels, 500 g/arm (Fed. Std. 191A, Method 5306)                                                                                          | Print legible after 100 cycles                                                                                                                                                                                                               |
| Chemical Vapor Phase Resistance     | Label adhered to epoxy PC board and exposed to the vapor of boiling chemical for 10 minutes and then rubbed with a cotton swab saturated with the chemical for 10 rubs |                                                                                                                                                                                                                                              |
|                                     | Test samples were baked 4 minutes at 160°C prior to testing.                                                                                                           |                                                                                                                                                                                                                                              |
|                                     | Ionox® 3955<br><br>Micronox® MX 2501                                                                                                                                   | Severe print removal<br><br>Complete print removal                                                                                                                                                                                           |

\*B-717 is not recommended for outdoor use.

| PERFORMANCE PROPERTY | CHEMICAL RESISTANCE |
|----------------------|---------------------|
|----------------------|---------------------|

Test samples were printed with the Brady Series R6000 Halogen Free ribbon. Labels were adhered to epoxy PC board. Test samples were exposed to the indicated environments. Test samples were baked 4 minutes at 160°C before testing. All test samples were immersed in the test fluids for 10 minutes prior to rub with cotton swab ten times.

| CHEMICAL REAGENT                               | SUBJECTIVE OBSERVATION TO VISUAL CHANGE |                    |          |
|------------------------------------------------|-----------------------------------------|--------------------|----------|
|                                                | EFFECT TO LABEL                         | R6000 HALOGEN FREE |          |
|                                                |                                         | WITHOUT RUB        | WITH RUB |
| Kyzen Corp, 15% Aquanox® A4625 at 140°F (60°C) | No visible effect                       | 1                  | 4        |
| Kyzen Corp, 17% Aquanox® A4520 at 140°F (60°C) | No visible effect                       | 1                  | 3        |
| Kyzen Corp, 10% Aquanox® A4638 at 150°F (65°C) | No visible effect                       | 1                  | 1        |
| Kyzen Corp, 20% Aquanox® A4703 at 145°F (63°C) | No visible effect                       | 1                  | 1        |
| Zestron, 15% Atron® AC205 at 150°F (65°C)      | No visible effect                       | 1                  | 5        |
| Zestron, 15% Atron® AC207 at 150°F (65°C)      | No visible effect                       | 1                  | 5        |
| Zestron, 15% Vigon® A201 at 150°F (65°C)       | No visible effect                       | 1                  | 5        |
| Zestron, 15% Vigon® N600 at 150°F (65°C)       | No visible effect                       | 1                  | 5        |
| Isopropyl Alcohol 99% at 180°F (82°C)          | No visible effect                       | 1                  | 2        |
| Deionized water at 212°F (100°C)               | No visible effect                       | 1                  | 1        |

Rating Scale:

- 1=no visible effect
- 2=slight smear or print removal, detectable but minimal smear
- 3=moderate smear or print removal (print still legible)
- 4=severe smear or print removal (print illegible or just barely legible)
- 5=complete print removal

| PERFORMANCE PROPERTY | TEST METHOD               |
|----------------------|---------------------------|
| Chemical Resistance  | MIL-STD-202G, Method 215K |

Test samples were printed with the Brady Series R6000 Halogen Free ribbon. Labels were printed with alphanumerics and bar codes. Test samples were subjected to 3 cycles of 3 minute immersions immediately followed by a toothbrush rub after each immersion.

| TEST FLUID                                       | RESULTS R6000 HALOGEN FREE |
|--------------------------------------------------|----------------------------|
| Solvent A<br>1 part IPA, 3 parts Mineral Spirits | Meets requirements         |
| Solvent C<br>Terpene Defluxer                    | Meets requirements         |
| Solvent D<br>Saponifier @ 70°C                   | Meets requirements         |

#### Shelf Life:

Shelf life is two years from the date of receipt for this product as long as this product is stored in its original packaging in an environment below 80° F (27° C) and 60% RH. It remains the responsibility of the user to assess the risk of using this product. We encourage customers to develop testing protocols that will qualify a product's fitness for use in their actual application.

#### Trademarks:

ANSI: American National Standards Institute (U.S.A.)  
ASTM: American Society for Testing and Materials (U.S.A.)  
All S.I. Units (metric) are mathematically derived from the U.S. Conventional Units  
Aquanox® is a registered trademark of the Kyzen Corporation

Atron® is a registered trademark of the Zestron Corporation  
lonox® is a registered trademark of the Kyzen Corporation  
Micronox® is a registered trademark of the Kyzen Corporation  
PSTC: Pressure Sensitive Tape Council (U.S.A.)  
Polyken™ is a trademark of Testing Machines Inc.  
UL: Underwriters Laboratories Inc. (U.S.A.)  
Vigon® is the registered trademark of Zestron Corporation  
Weather-Ometer® is a registered trademark of Atlas Material Testing Technology LLC

**Note:** All values shown are averages and should not be used for specification purposes.

Test data and test results contained in this document are for general information only and shall not be relied upon by Brady customers for designs and specifications, or be relied on as meeting specified performance criteria. Customers desiring to develop specifications or performance criteria for specific product applications should contact Brady for further information.

Product compliance information is based upon information provided by suppliers of the raw materials used by Brady to manufacture this product or based on results of testing using recognized analytical methods performed by a third party, independent laboratory. As such, Brady makes no independent representations or warranties, express or implied, and assumes no liability in connection with the use of this information.

## **WARRANTY**

Brady products are sold with the understanding that the buyers will test them in actual use and determine for themselves their adaptability to their intended uses. Brady warrants to the buyers that its products are free from defects in material and workmanship, but limits its obligation under this warranty to replacement of the product shown to Brady's satisfaction to have been defective at the time Brady sold it. This warranty does not extend to any persons obtaining the product from the buyers. This warranty is in lieu of any other warranty, express or implied, including, but not limited to, any implied warranty of merchantability or fitness for a particular purpose, and of any other obligations or liability on Brady's part. Under no circumstances will Brady be liable for any loss, damage, expense, or consequential damages of any kind arising in connection with the use, or inability to use, Brady's products.

Copyright 2019 Brady Worldwide, Inc. | All Rights Reserved  
Material may not be reproduced or distributed in any form without written permission.

---

Brady North America | 6555 W. Good Hope Rd | Milwaukee, WI 53223 | USA | Tel: 414-358-6600 | Fax: 800-292-2289