

N-Channel JFET

2N4859 2N4859A
2N4860 2N4860A
2N4861 2N4861A



SOLID STATE INC.

46 FARRAND STREET
BLOOMFIELD, NEW JERSEY 07003

www.solidstateinc.com

Common Uses


Analog switches
Multiplexer
Sample and hold
Choppers

Features

Low on resistance
High off resistance
Low C_{ps}
High speed switch

Absolute Maximum Ratings (25 °C)

Gate-source - 30 V
Gate-drain - 30 V
Drain-source ± 30 V
Gate current 10 mA
Device dissipation
(at or below 25 °C free air temperature) 300 mW
Storage range - 65° to + 200 °C



TO18

Bottom View

Electrical Characteristics (25 °C unless specified)

DC

			2N4859 2N4859A		2N4860 2N4860A		2N4861 2N4861A		Units
Characteristic	Symbol	Test Conditions	Min	Max	Min	Max	Min	Max	
1. Gate reverse current	I_{GSS}	$V_{DS} = 0, V_{GS} = -20$ V		- 0.25		- 0.25		- 0.25	nA
2.		$T_A = 150$ °C		- 0.5		- 0.5		- 0.5	μ A
3. Gate-channel break-down voltage	BV_{GSS}	$V_{DS} = 0, I_G = -1$ μ A	- 30		- 30		- 30		V
4. Gate-source cut off voltage	$V_{GS} (off)$	$V_{DS} = 15$ V, $I_D = 0.5$ nA	- 4	- 10	- 2	- 6	- 0.8	- 4	
5. Drain-source voltage	$V_{DS} (on)$	$V_{GS} = 0$ $I_D = 20$ mA		0.75					
6.		$I_D = 10$ mA				0.5			
7.		$I_D = 5$ mA						0.5	
8. Saturation drain current (Note 1)	I_{DSS}	$V_{DS} = 15$ V, $V_{GS} = 0$	50		20	100	8	80	mA
9. Drain cut off current	$I_D (off)$	$V_{DS} = 15$ V, $V_{GS} = -10$ V		0.25		0.25		0.25	nA
10.		$T_A = 150$ °C		0.50		0.50		0.50	μ A

AC

			Min	Max	Min	Max	Min	Max	Units
11. Input capacitance	C_{iss}	$V_{DS} = 0, V_{GS} = -10$ V		18		18		18	pF
12.		$f = 1$ MHz		10		10		10	
13. Feedback capacitance	C_{rss}			8		8		8	
14.				4		3.5		3.5	
15. Drain-source on resistance	$r_{ds} (on)$	$V_{DS} = 0, I_D = 0$ $f = 1$ kHz		25		40		60	ohms

Switching

			Min	Max	Min	Max	Min	Max	Units
16. Turn-on delay time	$t_d (on)$	$V_{DD} = 10$ V, $V_{GS} (on) = 0$		5		6		8	ns
17. Rise time	t_r	$I_D (on) \quad V_{GS} (off) \quad R_L$ 2N4859, A 20 mA - 10 V 464 Ω		3		4		8	
18. Turn-off time	$t (off)$	2N4860, A 10 mA - 6 V 953 Ω		20		40		80	
		2N4861, A 5 mA - 4 V 1910 Ω							

Notes: 1. Pulse test required, pulse width = 300 μ s, duty cycle $\leq$ 3%.

N-Channel JFET

FOR










Analog switches
Chopper
Commutators

PACKAGES:

TO18

2N4856-61
2N4856A-61A

Typical Characteristics (25°C unless otherwise noted)



Packaging Information

TO-18
(3 PIN)

