

# 3M Fibre Connectivity

## Coloured Pigtail Modules

Preliminary



These coloured pigtails complement the use of colour coded fibre in loose tube cables. Usually 12 different colours are used in either IEC or Bellcore coding. These pigtails use the same 12 colours, thus can be used for applications with both colour codes. The use of these colour coded pigtails makes the termination of fibre cable in patch panels or termination terminals easier and safer. Due to clear dedications, the risk of wrong fibre connections is reduced.

Two times 6 each semi.tight buffered pigtails in different standard colours are wrapped around two cardboard carriers and packed in a plastic bag.

---

### Features

- Wrapped around cardboard carrier
- 12 different colours
- For all commonly used connector types


### Benefits

- More convenient fibre management
- Easier connection to backbone cable
- Universal solution for all fibre patch panels


---

### Specifications:

|                                  |                                                                                 |
|----------------------------------|---------------------------------------------------------------------------------|
| <b>Pigtail length :</b>          | 2m                                                                              |
| <b>Pigtail colours IEC 304 :</b> | Red, green, blue, yellow, white, grey, brown, violet, aqua, black, orange, rose |
| <b>Pigtail type:</b>             | 900µm Semi-tight buffer                                                         |



Perfect fit to 3M Eco patch panels but fits any other 19" panel as SPP3-E type



## Ordering Information

### Description

ST Pigtail Multimode 50/125, 2m, 12 each in different IEC colour code  
 ST Pigtail Multimode 62,5/125, 2m, 12 each in different IEC colour code  
 SC Pigtail Multimode 50/125, 2m, 12 each in different IEC colour code  
 SC Pigtail Multimode 50/125, 2m, OM3, 12 each in different IEC colour code  
 SC Pigtail Multimode 62,5/125, 2m, 12 each in different IEC colour code  
 SC Pigtail Single-mode 9/125, 2m, 12 each in different IEC colour code  
 SC/UPC Pigtail Single-mode 9/125, 2m, 12 each in different IEC colour code  
 LC Pigtail Multimode 50/125, 2m, 12 each in different IEC colour code  
 LC Pigtail Multimode 50/125, 2m, OM3, 12 each in different IEC colour code  
 LC Pigtail Multimode 62,5/125, 2m, 12 each in different IEC colour code  
 LC Pigtail Single-mode 9/125, 2m, 12 each in different IEC colour code  
 LC/UPC Pigtail Single-mode 9/125, 2m, 12 each in different IEC colour code  
 FC Pigtail Single-mode 9/125 yellow, 2m, 12 each in different IEC colour code

### MOQ/each

6/bag/2bags/Carton  
 6/bag/2bags/Carton  
 6/bag/2bags/Carton  
 6/bag/2bags/Carton  
 6/bag/2bags/Carton  
 6/bag/2bags/Carton  
 6/bag/2bags/Carton  
 6/bag/2bags/Carton  
 6/bag/2bags/Carton  
 6/bag/2bags/Carton  
 6/bag/2bags/Carton  
 6/bag/2bags/Carton

### Ref.

**BANOO-ZK0002-CC**  
**BANOO-AP0002-CC**  
**BDBOO-ZK0002-CC**  
**BDBOO-ZO0002-CC**  
**BDBOO-AP0002-CC**  
**ADAOO-AU0002-CC**  
**AEQOO-AU0002-CC**  
**BDUOO-ZK0002-CC**  
**BDUOO-ZO0002-CC**  
**BDUOO-AP0002-CC**  
**ADVOO-AU0002-CC**  
**ADQOO-AU0002-CC**  
**AENOO-AU0002-CC**

### Packaging



Two bags in one box are the MOQ of 12 coloured pigtails

## Ordering Information Accessories (not included)

|                                                                                     | Description                                                                                                                                                                                                 | MOQ/each | Ref. No.                     |
|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------|------------------------------|
|    | <b>LWL-Spleißkassette</b><br>inkl. Zugentlastung, div. Kabelbindern, ohne Spleißschutzhalter<br>Maße: 155 x 92 x 8 mm (HxBxT)<br>Farbe: RAL 9001 (cremeweiß), VPE: 10 Stück                                 |          | 29026-500 31                 |
|    | <b>LWL-Spleißkassette</b><br>inkl. Spleißschutzhalter für 12x Crimpspleißschutz und<br>div. Kabelbindern, ohne Zugentlastung<br>Maße: 155 x 92 x 8 mm (HxBxT)<br>Farbe: RAL 9001 (cremeweiß), VPE: 30 Stück |          | 29026-500 30                 |
|    | <b>LWL-Deckel</b><br>für Spleißkassette, Farbe: RAL 9001 (cremeweiß)<br>Maße: 155 x 92 x 2 mm (HxBxT)<br>VPE: 10 Stück<br>VPE: 50 Stück                                                                     |          | 29025-503 31<br>29025-503 30 |
|    | <b>DIN Spleißkassette Scharnier rot</b><br>zum Verbinden von Spleißkassette und Deckel                                                                                                                      |          | 03-756-00500                 |
|  | <b>LWL-Zugentlastung</b><br>für 12 Fasern mit Ø 0.9 und 1.1 mm Coating<br>VPE: 50 Stück                                                                                                                     |          | 29031-000 30                 |
|  | <b>LWL-Spleißschutzhalter Crimp</b><br>VPE: 10 Stück, für 12x Crimpspleißschutz                                                                                                                             |          | 05-760-08000                 |
|  | <b>LWL-Crimpspleißschutz</b><br>VPE: 150 Stück                                                                                                                                                              |          | 05-760-08100                 |
|  | <b>LWL-Spleißschutzhalter Heißschrumpf</b><br>VPE: 10 Stück, für 6x Schrumpfspleißschutz                                                                                                                    |          | 05-760-11900                 |
|  | <b>LWL-Heißschrumpfspleißschutz 60 mm</b><br>VPE: 100 Stück                                                                                                                                                 |          | 05-760-12000                 |
|  | <b>LWL-Heißschrumpfspleißschutz 45 mm</b><br>VPE: 100 Stück                                                                                                                                                 |          | 05-760-12100                 |
|  | <b>LWL-Spleißschutzhalter Fibrlok™ Universal</b><br>VPE: 20 Stück, für 6x FibrLok                                                                                                                           |          | 2529-H                       |



**3M Telecommunications**  
Europe, Middle East & North Africa  
c/o Quante AG  
Carl-Schurz-Staße 1 • 41453 Neuss • Germany

Tel: ++49 (0)2131 / 14-5999  
Fax: ++49 (0)2131 / 14-5998  
Internet: [www.3MTelecommunications.com](http://www.3MTelecommunications.com)