


How to Order Additional Options:

2 DIGIT SERIES	INSULATION TYPE	TOTAL POLES	ACTIVE POSITIONS	CONTACT TYPE	TERMINAL TYPE	INDEX ANGLE	STOP TYPE	SHAFT/ BUSHING	SHAFT FLAT
C2	P-POLYESTER	01 - MIN.	08 - MAX @ 30° 04 - MAX @ 60° 03 - MAX @ 90°	N - NON SHORTING S - SHORTING		30° 60° 90°	F - FIXED C - CONT. A - ADJ.		
C3	P-POLYESTER	01 - MIN.	12 - MAX @ 30° 06 - MAX @ 60° 04 - MAX @ 90°	N - NON SHORTING S - SHORTING				SEE CHART "A"	SEE CHART "B"
CUSTOMERS SPECIFIED ORDER NUMBER FOR STANDARD OPTIONS									
	P			(SPECIFY)		(SPECIFY)		(SPECIFY)	(SPECIFY)
ADDITIONAL OPTIONS									

PRINTED CIRCUIT BOARD PATTERN



NOTES:

1. The standard spacing for the 1/8" dia. shaft from the first row of terminals to the mounting surface is .390 in.
2. The standard spacing for the 1/4" dia. shaft from the first row of terminals to the mounting surface is .481 in.

SHAFT AND FLAT OPTIONS





Chart A 1/8" shaft		
P/N OPT	Shaft Lgth	
01	1/4	Std.
02	3/8	
03	1/2	
04	9/16	
05	3/4	
06	7/8	
07	1	

Chart A 1/4" shaft		
P/N OPT	Shaft Lgth	
08	1/4	
09	3/8	
10	1/2	
11	9/16	
12	3/4	
13	7/8	
14	1	

CHART "B"	
P/N OPT	FLAT ANGLE
U	15°
W	165°
Y	195°
Z	345°

SHAFT AS VIEWED
WITH NON-TURN LUG
AT 9 O'CLOCK AND
SHAFT IN EXTREME
CCW POSITION AND
STRUT BOLTS
ORIENTED VERTICALLY.

C3 - DIMENSIONS - 12 PIN DESIGN



CUSTOM SWITCHES ARE AVAILABLE. CONTACT THE FACTORY WITH YOUR COMPLETE SPECIFICATIONS.



ELECTROSWITCH • ELECTRONIC PRODUCTS

UNIT OF ELECTRO SWITCH CORP.

2010 Yonkers Road
Raleigh, NC 27604

Telephone: (888) ROTARYS or (919) 833-0707
Fax: (800) 909-9171 or (919) 833-8016

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Electroswitch:

[C3P0206N-A](#) [C3P0212N-A](#) [C3P0112N-A](#) [C3P0304N-A](#) [C3P0406N-A](#) [C3P0604N-A](#) [C3P0206S-A](#) [C2P0404N-A](#)
[C3P0212S-A](#) [C2P0508S-A](#) [C3P0412N-A](#)