


APPLY TO PRODUCTS MADE BY MOLEX MALAYSIA



注記 NOTES △ 接点部までの嵌合長さ。
LENGTH TO CONTACT POINT.




2. 使用材料 MATERIAL
ハウジング : 46ナイロン (耐熱性), UL94V-0
アクチュエータ : PPS, UL94V-0
ターミナル : リン青銅, 錫ビスマスメッキ (t=0.32)
金具 : リン青銅, 錫メッキ (t=0.25)
FITTING NAIL : PHOSPHOR BRONZE, TIN OVER NICKEL PLATING. (t=0.25)

- △ パターンはくり止め用金具
FITTING NAIL FOR PREVENTION OF PEELING OF P.C.B. PATTERN.
4. エンボステープ梱包時は、アクチュエータがロックした状態とする。
IN THE PACKAGE, ACTUATOR OF PART NO. 52207-**-56 SHOULD BE LOCKED.

- △ FPC挿入深さ
INSERTION DEPTH OF FPC.

- △ パターン書き込み禁止エリア。
NO FOOT PRINT AREA.

7. SIMILAR ITEM : 52207-**-58



34.7	31.2	29	52207-3056	30
33.7	30.2	28	-2956	29
32.7	29.2	27	-2856	28
31.7	28.2	26	-2756	27
30.7	27.2	25	-2656	26
29.7	26.2	24	-2556	25
28.7	25.2	23	-2456	24
27.7	24.2	22	-2356	23
26.7	23.2	21	-2256	22
25.7	22.2	20	-2156	21
24.7	21.2	19	-2056	20
23.7	20.2	18	-1956	19
22.7	19.2	17	-1856	18
21.7	18.2	16	-1756	17
20.7	17.2	15	-1656	16
19.7	16.2	14	-1556	15
18.7	15.2	13	-1456	14
17.7	14.2	12	-1356	13
16.7	13.2	11	-1256	12
15.7	12.2	10	-1156	11
14.7	11.2	9	-1056	10
13.7	10.2	8	-0956	9
12.7	9.2	7	-0856	8
11.7	8.2	6	-0756	7
10.7	7.2	5	-0656	6
9.7	6.2	4	-0556	5
8.7	5.2	3	-0456	4
7.7	4.2	2	52207-0356	3
C	B	A	MATERIAL NO.	CIRCUIT


REVISED	EC NO: J2006-3500	2006/05/16	2006/05/19	2006/05/25
DRWN: A0YAGI	CHKD: MTANAKA	APPR: NUKITA		
DESCRIPTION				
REV	A			

GENERAL TOLERANCES (UNLESS SPECIFIED)	
10 UNDER	±0.2
10 OVER 30 UNDER	±0.25
30 OVER	±0.3
ANGULAR	±3 °
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	

DIMENSION STYLE MM ONLY	
DRAWN BY	DATE
Y. SAKIYA	2004/07/28
CHECKED BY	DATE
M. SASAO	2004/07/28
APPROVED BY	DATE
M. SASAO	2004/07/28
MATERIAL NO.	
SIZE	
A3	

52207-**x56		MODEL NO.	
SCALE ---	DESIGN UNITS METRIC		THIRD ANGLE PROJECTION
TITLE			
1.0MM FPC CONN ZIF SMT			
-LEAD FREE-			
 MOLEX INCORPORATED			
DOCUMENT NO. SD-52207-062			SHEET NO. 1 OF 2
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			

APPLY TO PRODUCTS MADE BY MOLEX MALAYSIA



下面图



REVISED	EC NO: J2006-3500	2006/05/16
	DRWN: YAOYAGI	2006/05/19
	CHKD: MTANAKA	2006/05/19
	APPR: NUKITA	2006/05/25
A	REV	

GENERAL TOLERANCES (UNLESS SPECIFIED)	
10 UNDER	± 0.2
10 OVER 30 UNDER	± 0.25
30 OVER	± 0.3
ANGULAR	± 3 °
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	

DIMENSION STYLE MM ONLY	
DRAWN BY	DATE
Y. SAKIYA	2004/07/28
CHECKED BY	DATE
M. SASAO	2004/07/28
APPROVED BY	DATE
M. SASAO	2004/07/28
MATERIAL NO.	
SEE SHEET 1 OF 2	
SIZE	
A3	

52207-**-56		MODEL NO.	
SCALE 10:1	DESIGN UNITS METRIC		THIRD ANGLE PROJECTION
TITLE 1.0MM FPC CONN ZIF SMT			
-LEAD FREE-			
 MOLEX INCORPORATED			
DOCUMENT NO. SD-52207-062			SHEET NO. 2 OF 2
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			

APPLY TO PRODUCTS MADE BY MOLEX MALAYSIA



DETAIL H

注記


1. 製品番号 52207-**56 の梱包状態はアクチュエータがロックした状態とする。
詳細寸法については図面 SD-52207-062 を参照下さい。

IN THE PACKAGE , ACTUATOR OF PART NO. 52207-**56 SHOULD BE LOCKED
RE DETAILED DIMENSIONS , SEE SD-52207-062.

2. 梱包数量 : 1000個/リール
NUMBER OF CONNECTORS : 1000PCS/REEL

3. リードテープ長さ(LEAD TAPE LENGTH)

トップテープ TOP TAPE リーダー部 LEADER PART 未接着部 NON-BONDED PART




4. トップテープの剥離強度 : 0.1~1.3 N (10~130 gf) (剥離方向は下図参照)
尚、本規格値は、出荷時に適用。(但し、輸送時に剥離が発生しない事。)

PEELING OFF FORCE OF TOP TAPE : 0.1~1.3 N (10~130 gf)

(PEELING DIRECTION AS SHOWN IN FOLLOWING FIG.)

THIS REQUIREMENT SHOULD BE APPLIED AT SHIPMENT.(PEEL OFF SHOULD NOT BE ALLOWED , DURING TRANSPORTATION.)



5. 材料(MATERIAL)

キャリアテープ (CARRIER TAPE) : ポリプロピレン (POLYPROPYLENE)

トップテープ (TOPTAPE) : PET, PE, PEF

リール (REEL) : ポリスチレン (PS) <リサイクル材を含む>

POLYSTYRENE (PS) <RECYCLE MATERIAL CONTAINED>

6. SIMILAR ITEM : 52207-**82


REV	DESCRIPTION
REVISED	EC NO: J2006-3527
	DRWN:YAOYAGI 2006/05/19
	CHKD:MTANAKA 2006/05/19
	APPR:NUKITA 2006/05/19
A	

GENERAL TOLERANCES (UNLESS SPECIFIED)	
10 UNDER	± 0.2
10 OVER 30 UNDER	± 0.25
30 OVER	± 0.3
ANGULAR	$\pm 3^{\circ}$
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	

DIMENSION STYLE MM ONLY	
DRAWN BY	DATE
Y.SAKIYA	2004/07/28
CHECKED BY	DATE
M.SASAO	2004/07/28
APPROVED BY	DATE
M.SASAO	2004/07/28
MATERIAL NO.	
SEE SHEET 2,3,4	
SIZE	
A3	


52207-**83		MODEL NO.
SCALE ---	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION
TITLE		
EMBSTP PKG FOR 1.0MM FPC CONN ZIF SMT -LEAD FREE-		
MOLEX INCORPORATED		
DOCUMENT NO.	SHEET NO.	
SD-52207-063	1 OF 4	

APPLY TO PRODUCTS MADE BY MOLEX MALAYSIA




SECT:T-T

16mm 幅 キャリアテープ
16mm WIDTH CARRIER TAPE



SECT:X-X

24mm 幅 キャリアテープ
24mm WIDTH CARRIER TAPE




SECT:V-V
SCALE (5:1)

24	29.4	25.4	18.5	15	11.7	17.3	52207-1183	11
			17.5	14	10.7	16.3	4 -1083	10
			16.5	13	9.7	15.3	-0983	9
			15.5	12	8.7	14.3	-0883	8
			14.5	11	7.7	13.3	-0783	7
			13.5	10	6.7	12.3	-0683	6
			12.5	9	5.7	11.3	-0583	5
16	21.4	17.4	11.5	8	4.7	10.3	7 -0483	4
キャリアテープ幅 CARRIER TAPE WIDTH	F	E	(D)	(C)	(B)	(A)	MATERIAL NO.	CIRCUIT

REVISED EC NO: J2006-3527 DRWN: YAOYAGI CHKD: MTANAKA APPR: NUKITA	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 2:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	
		10 UNDER	± ---	DRAWN BY Y. SAKIYA	DATE 2004/07/28	TITLE EMBSTP PKG FOR 1.0MM FPC CONN ZIF SMT -LEAD FREE-			
		10 OVER 30 UNDER	± ---	CHECKED BY M. SASAO	DATE 2004/07/28				
		30 OVER	± ---	APPROVED BY M. SASAO	DATE 2004/07/28	 MOLEX INCORPORATED			
		ANGULAR ± --- °		MATERIAL NO.					
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE SHEET 23.4		SD-52207-063		2 OF 4		
	REV A	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							

APPLY TO PRODUCTS MADE BY MOLEX MALAYSIA



32	37.4	33.4	4.0	0.5	23.5	20	16.7	22.35	52207-1683	16	
			4.2	0.6	22.5	19	15.7	21.35	4	-1583	15
			4.2	0.6	21.5	18	14.7	20.35		-1483	14
			4.2	0.6	20.5	17	13.7	19.35	7	-1383	13
			4.2	0.6	19.5	16	12.7	18.35	52207-1283		12
キャリアテープ幅 CARRIER TAPE WIDTH	F	E	(G)	(F)	(D)	(C)	(B)	(A)	MATERIAL NO.	CIRCUIT	

44	49.4	45.4	34.5	31	27.7	33.35	52207-2783	27	
			33.5	30	26.7	32.35	4	-2683	26
			32.5	29	25.7	31.35		-2583	25
			31.5	28	24.7	30.35		-2483	24
			30.5	27	23.7	29.35		-2383	23
			29.5	26	22.7	28.35		-2283	22
			28.5	25	21.7	27.35		-2183	21
			27.5	24	20.7	26.35		-2083	20
			26.5	23	19.7	25.35		-1983	19
			25.5	22	18.7	24.35	7	-1883	18
			24.5	21	17.7	23.35		52207-1783	17
キャリアテープ幅 CARRIER TAPE WIDTH	F	E	(D)	(C)	(B)	(A)	MATERIAL NO.	CIRCUIT	

REVISED EC NO: J2006-3527 DRWN:YAOYAGI 2006/05/19 CHKD:MTANAKA 2006/05/19 APPR:NUKITA 2006/05/19 A	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 2:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
		10 UNDER	± ---	DRAWN BY Y. SAKIYA	DATE 2004/07/28	TITLE EMBSTP PKG FOR 1.0MM FPC CONN ZIF SMT -LEAD FREE-				
		10 OVER 30 UNDER	± ---	CHECKED BY M. SASAO	DATE 2004/07/28					
		30 OVER	± ---	APPROVED BY M. SASAO	DATE 2004/07/28	MOLEX MOLEX INCORPORATED				
		ANGULAR ± --- °		MATERIAL NO.		DOCUMENT NO.		SHEET NO.		
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE SHEET 2,3,4		SD-52207-063		3 OF 4		
	REV		SIZE A3 THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							

