



1. DIMENSIONS SHOWN ARE MAXIMUM UNLESS OTHERWISE SPECIFIED.
2. CALBE ASSEMBLY IS WIRED PER ELECTRICAL DIAGRAM.
3. MATERIAL:
CONNECTOR HOUSINGS - POLYCARBONATE, UL 94V-0, BLACK,
STRAIN RELIEFS - CARBON STEEL WITH NICKEL PLATING
5.08µm [.0002001] MINIMUM THICK.
CONTACTS - COPPER ALLOY WITH SILVER PLATED STRIP
3.81µm [.0001501] MINIMUM THICK.
4. DIMENSION "A" SHALL BE MEASURED WITH CONDUIT
IN THE RELAXED POSITION.
5. DESIGNATIONS IN PARENTHESES () ARE FOR
REFERENCE ONLY.
6. MANUFACTURING LOCATION, DATE CODE, PART
NUMBER AND LENGTH SHALL BE INK STAMPED WHERE
INDICATED.
7. APPLICATION:
AMPINERGY™ MODULAR WIRING SYSTEM, A
MANUFACTURED WIRING SYSTEM.
8. USE GROUNDED WIRE INSPECTION WINDOW TO
VERIFY BONDING AND GROUNDING CONDUCTOR.



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG. 19DEC01 CHK. T. PITTS L. SMITH 02JAN02 APVD. F. LINCOLN 02JAN02		 TE Connectivity	
DIMENSIONS: MM [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±. 1 PLC ±. 2 PLC ±. 3 PLC ±. ANGLES ±. FINISH		NAME CABLE ASSEMBLY, POWER TO LINE, 8 WIRE -	
		PRODUCT SPEC APPLICATION SPEC -		SIZE CAGE CODE DRAWING NO A1 00779 C=556731	
MATERIAL - 3		WEIGHT - 3		RESTRICTED TO -	
CUSTOMER DRAWING		SCALE		SHEET OF REV V	