



Products
>
Data Converters
>
Analog to Digital Converters (ADC)
>
High Speed Parallel Interface Adc
>
ADC1112D125F2 demo board; LVDS/DDR version;

Download Manual - Software



Status:

Obsolete

Product Quick Links

Product Options

Technical Documentation

Software & Tools

Related Products

Contact Sales

ADC1112D125F2

ADC1112D125F2 demo board; LVDS/DDR version;

IDT's dual-channel ADC demoboard is suitable for dynamic performance evaluations from low to high IF configuration with LVDS/DDR output variants. A data-acquisition board can be used during design and prototype to analyze ADC performance.



Features

- SMA connector for clock and analog inputs signal
- LVDS/DDR output

Product Options

Orderable Part ID	Part Status	Pkg. Code	Pkg. Type	Lead Count (#)	Temp. Grade	Pb (Lead) Free	Sample & Buy
ADC1112D125F2-DB	Obsolete	BD0	BOARD	0	I	No	Check Availability

Technical Documentation

	Title	Type	Format	File Size	Date
User Guides & Manuals					
	Demo Board Software ADC_1_r04	Manual - Software	ZIP	2.33 MB	07/19/2012

Related Products

Product ID	Title
ADC1112D125HN	Dual 11-bit ADC; CMOS or LVDS DDR digital outputs

GET TECHNICAL SUPPORT

CONTACT SALES OFFICE