




Description

- Industry standard leaded package
Resistance welded, hermetically sealed in an inert atmosphere, glass to metal seals on leads
- 2 Leg design
- Model HC49/4H
- Model Issue number 15



Frequency Parameters

- Frequency 20.0MHz
- Frequency Tolerance @ 25°C ±30.00ppm
- Frequency Stability ±50.00ppm
- Operating Temperature Range -20.00 to 70.00°C
- Overtone Order Fundamental
- Ageing ±5ppm typical per year at 25°C

Electrical Parameters

- Load Capacitance (CL) 12.00pF
- Shunt Capacitance (C0) 7pF max
- Drive Level 500µW max
- ESR 40Ω max

Environmental Parameters

- Shock: 981m/s², 6ms, 3 times in each of 3 mutually perpendicular planes
- Vibration: 10Hz-60Hz, 0.75mm amplitude, 60Hz-500Hz, 98.1m/s², 30mins in 3 mutually perpendicular planes
- Storage Temperature Range: -55 to 125°C

Compliance


- RoHS Status Compliant
- REACH Status Compliant

Packaging

- Pack Type: Bulk Loose in Bulk pack
- Pack Size 100
- Alternative packing option available


This document is correct at the time of printing; please contact your local office for the latest version.

Outline (mm)



Underside View

Typical Frequency vs Temperature Curves



Sales Office Contact Details:

UK: +44 (0)1460 270200

France: +33 (0)5 34 50 91 18

Email: info@iqdfrequencyproducts.com

Germany: +49 (0)7264 9145-0

USA: +1 (0) 408 455 2426

Web: www.iqdfrequencyproducts.com