

ORDERING INFORMATION

E 842 - 816 - XX XX - X XX X

Date code _____
Nil - No date code
E - Date code printed 

No. of contact _____

Body & pin configuration _____
(Refer to Table III)

Lock & Eject (L&E) and mounting stud options _____

- 0 - no L&E, no stud
1 - short L&E, no stud
2 - short L&E, short stud
3 - short L&E, long stud
4 - long L&E, no stud
5 - long L&E, short stud
6 - long L&E, long stud
F - long L&E, M2.5 stud

Nil - standard
S - standard with polarizing
key slot for size 10 

Plating
AA - gold flash duplex
19 - 15u" gold plated duplex
35 - 30u" gold plated duplex

Table III

Standard product - four side grey	Non-standard product - three side grey (specific quantity required)	K
30 - straight solder tail, for 0.062" [1.6 mm] PCB	20 - obsolete	0.109 ± 0.007 [2.61 ± 0.34] coined tail
31 - straight solder tail, for 0.125" [3.2 mm] PCB	21 - obsolete	0.171 ± 0.022 [4.14 ± 0.36] coined tail
32 - right angle solder tail, for 0.062" [1.6 mm] PCB	22 - obsolete	0.109 ± 0.007 [2.61 ± 0.34] coined tail
33 - right angle solder tail, for 0.125" [3.2 mm] PCB	23 - obsolete	0.171 ± 0.022 [4.14 ± 0.36] coined tail
37 - straight wire wrap tail	27 - obsolete	0.61 ± 0.015 [15.49 ± 0.38] square tail
39 - right angle wire wrap tail	29 - obsolete	0.61 ± 0.015 [15.49 ± 0.38] square tail

Recommended PCB layout







Table IV

Size	A	B	C	D	E	F
10	1.26 [32.07]	1.10 [27.94]	0.860 [21.84]	0.708 [17.98]	0.400 [10.16]	4
14	1.46 [37.08]	1.30 [33.02]	1.060 [26.92]	0.908 [23.06]	0.600 [15.24]	6
16	1.56 [39.62]	1.40 [35.56]	1.160 [29.46]	1.008 [25.60]	0.700 [17.78]	7
20	1.76 [44.70]	1.60 [40.64]	1.360 [34.54]	1.208 [30.68]	0.900 [22.86]	9
26	2.06 [52.32]	1.90 [48.26]	1.660 [42.16]	1.508 [38.30]	1.200 [30.40]	12
30	2.26 [57.40]	2.10 [53.34]	1.860 [47.24]	1.708 [43.38]	1.400 [35.56]	14
34	2.46 [62.48]	2.30 [58.42]	2.060 [52.32]	1.908 [48.46]	1.600 [40.64]	16
40	2.76 [70.10]	2.60 [66.04]	2.360 [59.94]	2.208 [56.08]	1.900 [48.26]	19
50	3.26 [82.80]	3.10 [78.74]	2.860 [72.64]	2.708 [68.78]	2.400 [60.96]	24
60	3.76 [95.50]	3.60 [91.44]	3.360 [85.34]	3.208 [81.48]	2.900 [73.66]	29
64	3.96 [100.58]	3.80 [96.52]	3.560 [90.42]	3.408 [86.60]	3.100 [78.74]	31



Customer Drawing

UNLESS OTHERWISE SPECIFIED TOLERANCES U.S. METRIC .X +/- .020 0.51 .XX +/- .010 0.25 .XXX +/- .005 0.13 FRACTIONS +/- ANGLES +/- 2.5° 2.5°	APPROVAL	DATE	Amphenol
	DRAWN ALEX.LEE	07/18/05	
	CHECKED TSUI	07/18/05	
	CHECKED		
FOR MATERIALS AND FINISHES SEE NOTES	DRAWING FILE : DRAWING_816_CB16.DWG		TITLE
REMOVE SHARP EDGES			816 Protected Header
DIMENSIONS	ANGLE OF PROJECTION		SIZE DRAWING NO.
U.S. INCHES			A3 C816-XXXX-XXX
METRIC MM			SCALE NONE
			SHEET 2 OF 2


This document is the property of Amphenol Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without the prior consent, and that no right is granted to disclose or to use any information in this document.




REVISIONS				
SYM	ECN	DESCRIPTION	DATE	APPROVED
Q	HK1421	RELEASE TO CUSTOMER	06/12/97	NELSON
R	HK1513	***TAIL SIZE MODIFIED	06/01/98	Michael Tsai
S	HK2043	Revise L&E options&delete three side option	8/24/01	Michael IP
T	HK3437	UPDATE DRAWING TO COMPLY WITH RoHS	07/18/05	Michael IP




** SQ. TAIL 0.025[0.64]
COILED TAIL 0.031[0.79] MAX.



Size 14
P/N: X842-816-14XX-XXX



Size 34 or above
P/N: X842-816-XXXX-XXX




Size 10 with CPK slot
P/N: 842-816-10XX-XXXS, or
P/N: E842-816-10XX-XXX with date code



Size 20
P/N: X842-816-20XX-XXX



Size 10 without CPK slot
P/N: 842-816-10XX-XXX



Size 16
P/N: X842-816-16XX-XXX




Table I

Latch & Eject	J	H
Short: for use with non strain relief socket	0.425 [10.80]	1.015 [25.78]
Long for use with strain relief socket	0.575 [14.61]	1.135 [28.83]

Table II

Stud	L	M
Short stud 2-56	0.29 [7.4]	0.45 [11.43]
Long stud 2-56	0.36 [9.1]	0.52 [13.21]
Stud M2.5	0.18 [4.6]	0.34 [8.6]

Note: unit in inch [mm]

UNLESS OTHERWISE SPECIFIED TOLERANCES

	U.S.	METRIC
.X +/-	.020	0.51
.XX +/-	.010	0.25
.XXX +/-	.005	0.13
FRACTIONS +/-		
ANGLES +/-	2.5°	2.5°

FOR MATERIALS AND FINISHES SEE NOTES

REMOVE SHARP EDGES

DIMENSIONS

U.S. INCHES


METRIC MM

APPROVAL DATE

DRAWN ALEX.LEE	07/18/05
CHECKED TSUI	07/18/05
CHECKED	

DRAWING FILE: \DRAWING\816\CB816.DWG

ANGLE OF PROJECTION



Amphenol

TITLE

816 Protected Header

SIZE DRAWING NO. REV.

A3 C816-XXXX-XXX T

SCALE NONE SHEET 1 OF 2

Customer Drawing

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

[8428161632035](#) [8428165030035](#) [8428162030135](#) [8428163030419](#) [8428161030035](#) [8428162030035](#)
[8428163430035](#) [8428162630035](#) [8428164030035](#) [8428162032035](#) [84281650314AA](#) [84281620311AA](#)
[84281620334AA](#) [84281650311AA](#) [8428165031435](#) [84281650330AA](#) [84281650334AA](#)