

4184	9050	4353	9083
4184-0-00-XX-00-00-33-0 Solder mount in .014 mounting hole	9050-0-00-XX-00-00-33-0 Solder mount in .016 mounting hole	4353-0-00-XX-00-00-33-0 Solder mount in .016 mounting hole	9083-0-00-XX-00-00-38-0 Solder mount in .016 mounting hole
4825	4689	4361	4288
4825-0-00-XX-00-00-33-0 Solder mount in .019 mounting hole	4689-0-00-XX-00-00-33-0 Solder mount in .019 mounting hole	4361-0-00-XX-00-00-33-0 Solder mount in .022 mounting hole	4288-0-00-XX-00-00-33-0 Solder mount in .022 mounting hole
4068	9113	9137	5137
4068-0-00-XX-00-00-33-0 Solder mount in .022 mounting hole	9113-0-00-XX-00-00-38-0 Solder mount in .022 mounting hole	9137-0-00-XX-00-00-38-0 Solder mount in .022 mounting hole	5137-0-00-XX-00-00-38-0 Solder mount in .022 mounting hole
SPECIFICATIONS PIN MATERIAL: Brass Alloy 360, 1/2 Hard (Except where noted) DIMENSION IN INCHES TOLERANCES ON: LENGTHS: ±.005 DIAMETERS: ±.002 ANGLES: ± 2°	ORDER CODE: XXXX - X - 00 - XX - 00 - 00 - 3X - 0 BASIC PART # → SPECIFY PIN FINISH: 01 200μ" TIN/LEAD OVER NICKEL 80 200μ" TIN OVER NICKEL 15 10μ" GOLD OVER NICKEL 21 20μ" GOLD OVER NICKEL 34 50μ" GOLD OVER NICKEL		