

THA-266SUS Cam THA-266




Characteristic


Size can be selected for various mounting location.

Application


Various types of handles.




THA-266-1




THA-266-2
THA-266SUS-2




THA-266-3



THA-266-4



THA-266-5



THA-266SUS-1

Specification

Model No.	Net Weight (g)	Code No.
THA-266SUS-1	43.5	3712
THA-266-1	48.5	3701
THA-266SUS-2	17.0	3713
THA-266-2	17.0	3702
THA-266-3	17.0	3703
THA-266-4	34.5	3704
THA-266-5	62.0	3705

Model No.	Material	Finish
THA-266SUS	SUS304	—
THA-266	SPCC	Zn

THA-267SUS Cam THA-267




Characteristic


Size can be selected for various mounting location.

Application


Various types of handles.




THA-267-1



THA-267-2



THA-267-3
THA-267SUS-3



THA-267SUS-1

Specification

Model No.	Net Weight (g)	Code No.
THA-267SUS-1	44.5	3709
THA-267-1	47.0	3706
THA-267-2	60.0	3707
THA-267SUS-3	16.5	3711
THA-267-3	16.0	3708

Model No.	Material	Finish
THA-267SUS	SUS304	—
THA-267	SPCC	Zn