

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0026102171

Status:


Planned for Obsolescence

Overview:

kk

Description:

3.96mm (.156") Pitch KK® Header, Right Angle, Square Pin, 17 Circuits, Tin (Sn) Plating



Documents:

3D Model

Drawing (PDF)

Product Specification PS-99020-0087 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E29179
General	
Product Family	PCB Headers
Series	3246
Application	Board-to-Board, Power, Wire-to-Board
Overview	kk
Product Name	KK®

Physical	
Breakaway	No
Circuits (Loaded)	17
Circuits (maximum)	17
Color - Resin	Natural
Durability (mating cycles max)	25
Flammability	94V-2
Glow-Wire Compliant	No
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Number of Rows	1
Orientation	Right Angle
PC Tail Length	3.96mm (.156")
PCB Locator	No
PCB Retention	None
Packaging Type	Bag
Pitch - Mating Interface	3.96mm (.156")
Plating min - Mating	5.080µm (200µ")
Plating min - Termination	5.080µm (200µ")
Polarized to Mating Part	No
Polarized to PCB	No
Shrouded	No
Stackable	Yes
Temperature Range - Operating	0°C to +75°C
Termination Interface: Style	Through Hole

Electrical	
Current - Maximum per Contact	7A
Voltage - Maximum	250V

Solder Process Data	
Lead-free Process Capability	Wave Capable (TH only)

Material Info

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Not Reviewed

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com

For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

3246Series

Old Part Number	324617A
Reference - Drawing Numbers	
Product Specification	PS-99020-0087
Sales Drawing	SDA-3246-N

This document was generated on 05/03/2011

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION