


THIS DRAWING IS UNPUBLISHED.


RELEASED FOR PUBLICATION

© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AA	00		S	ECO-06-009878	27JULY06	LAM	AWF
			S1	REVISED PER ECO-09-021826	11JAN10	KK	AEG



1. WIRE RANGE 22-26 AWG.
2. INSULATION RANGE 0.91-1.37 [.036-.054] DIA.
3. 0.00254 [.000100] MIN TIN-LEAD OVER 0.000762 [.000030] MIN NICKEL.
4. PREPLATED 0.00127 [.000050] MIN TIN-LEAD IN ZONES I & II, 0.000762 [.000030] MIN GOLD OVER 0.000762 [.000030] MIN NICKEL INLAY IN ZONE III.
5. PREPLATED 0.00127 [.000050] MIN TIN-LEAD IN ZONES I & II, 0.00127 [.000050] MIN GOLD OVER 0.000762 [.000030] MIN NICKEL INLAY IN ZONE III.
6. PHOSPHOR BRONZE.
7. PREPLATED 0.00127 [.000050] MIN TIN IN ZONES I & II, 0.00127 [.000050] MIN GOLD OVER 0.000762 [.000030] MIN NICKEL INLAY IN ZONE III.
8. ZONE I (OUTSIDE SURFACES).
9. ZONE II (INSIDE SURFACES).
10. ZONE III (INSIDE SURFACES).
11. MAXIMUM CUTOFF.
12. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
13. OBSOLETE



SECTION Y-Y



SECTION Z-Z

12	OBSOLETE	7	-	9	530553-0
	OBSOLETE		530553-9		530553-8
		5	13	530553-7	530553-6
		4	13	530553-5	530553-4
SUPERSEDED BY 5530553-2		3	13	530553-3	530553-2
	FINISH		LOOSE PIECE PART NO		STRIP PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± 0.13[.005]
4 PLC ± -
ANGLES ± -

MATERIAL

6

DWN
B. HAYMAKER
08JAN99

CHK
S. BOLASH
08JAN99

APVD
S. BOLASH
08JAN99

PRODUCT SPEC
108-25031

APPLICATION SPEC
114-25021

WEIGHT
-

CUSTOMER DRAWING

Tyco Electronics Corporation
Harrisburg, PA 17105-3608

NAME
CONTACT, RECEPTACLE,
STANDARD PRESSURE,
MINI-TANDEM SPRING

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=530553

RESTRICTED TO
-

SCALE
4:1

SHEET
1 OF 1

REV
S1

5305530553