





PART NO.	DIM. "A"	DIM. "B"	DIM. "C"
WS-SE2-1-01	16.6 [.65]	10.5 [.41]	7.1 [.28]
WS-SE2-2-01	19.5 [.77]	13.4 [.53]	10 [.39]



WS-SE2-1



WS-SE2-2

- NOTES:
1. MATERIAL: NYLON 6/6 UL 94 V-2 (RMS-01).
NYLON 6/6 UL 94 V-0 (RMS-19), AVAILABLE BY SPECIAL ORDER ONLY.
TO ORDER REPLACE "-01" WITH "-19"
 2. COLOR: NATURAL.
 3. ALTERNATE UNITS FOR REFERENCE ONLY.

			TITLE: WIRE SADDLE SIDE ENTRY						DWG IN MM [IN]	
			CREATED USING SOLIDWORKS	FILE #: WS-SE2-X		DWN: SK	APP: RT		FINAL	
			GENERAL TOLERANCE UNLESS OTHERWISE NOTED ±0.25 ANG. ±1°	SHEET: 1 OF 1		SHEET SIZE: A		DT: 07/06/06		CHKD: SJ
				RE: RICHCO, INC.		RICHCO, INC.		ENG@RICHCO-INC.COM (773) 539-4060		
E	SEE ECN #1216 FOR CHANGES	SK	09/15/06					PART #		PRINT TYPE CA
D	SEE ECN #1191 FOR CHANGES	SK	07/06/06					SEE TABLE		
-	SEE ENGINEERING FOR REV A-C	-	---							
REV.	DESCRIPTION	ENGR.	DATE							