


LOW PROFILE SOCKET STRIPS

(2.54 mm) .100" PITCH • SLW/CES SERIES



SLW

Mates:

TLW, TSW, MTLW, MTSW,
HW, EW, ZW, HTSW,
HMTSW, TSM

CES

Mates:

TLW, TSW, MTLW,
MTSW, HW, EW, ZW,
DW, HTSW, PHT, HMTSW



SPECIFICATIONS

Insulator Material:

Black G.F. Polyester

Contact Material:

Phosphor Bronze

Plating:

Au or Sn over
50 μ " (1.27 μ m) Ni

Operating Temp Range:

-55 °C to +125 °C with Gold

-55 °C to +105 °C with Tin

Current Rating (SLW/TSW):

5.2 A per pin

(2 pins powered)

CES Current Rating (TSW/CES):

5.5 A per pin

(2 pins powered)

Voltage Rating:

SLW: 406 VAC/574 VDC

CES: 400 VAC/566 VDC

Insertion Depth:

SLW: (2.16 mm) .085" to

(2.92 mm) .115"

CES: (2.62 mm) .103" to

(4.06 mm) .160"

Lead-Free Solderable:

No, Lead Wave only

PROCESSING

Lead-Free Solderable:

No, Lead Wave only

ALSO AVAILABLE

Contact Samtec

Other Platings

SLW	-	1	NO. PINS PER ROW	-	01	-	PLATING OPTION	-	ROW OPTION
-----	---	---	------------------	---	----	---	----------------	---	------------

01 thru 50

-F

= Gold flash on contact,
Matte Tin on tail

-S

= Single Row

-L

= 10 μ " (0.25 μ m) Gold on contact,
Matte Tin on tail

-D





= Double Row

-G

= 20 μ " (0.51 μ m) Gold on contact,
Gold flash on balance

-T

= Matte Tin



CES	-	1	NO. PINS PER ROW	-	LEAD STYLE	-	PLATING OPTION	-	ROW OPTION	-	RA OPTION
-----	---	---	------------------	---	------------	---	----------------	---	------------	---	-----------

01 thru 50

Specify
LEAD
STYLE
from
chart

-F

= Gold flash
on contact,
Matte Tin on tail

-S

= Single Row

-RA

= Right-angle
version
(Style -02 only
Single Row only)

-D





= Double Row

-L

= 10 μ " (0.25 μ m)
Gold contact,
Matte Tin on tail

-T

= Matte Tin



LEAD STYLE	A
-01	(3.25) .128
-02	(5.66) .223

Note:
Some lengths, styles and
options are non-standard,
non-returnable.

samtec.com?SLW or samtec.com?CES

F-224 (Rev 25APR25)

Unless otherwise approved in writing by Samtec, all parts and components are designed and built according to Samtec's specifications which are subject to change without notice.