

FP20-600

Electrical Specifications (@25C)

1. Maximum Power: 12.0 VA
2. Primary Voltage:
 - Series: 230V@50/60 Hz
 - Parallel: 115V@50/60Hz
3. Secondary:
 - Series: 20.0VCT @ 0.600Amps
 - Parallel: 10.0V @ 1.20Amps

Description:

The FP20-600 is part of a series which has a long history of reliable service in the field, made from a proven design and constructed with UL recognized materials.

Construction:

Wound on two dual channel nylon bobbin. Materials are UL recognized, Class B (130° C) rated.

Safety:

These products are 100% hipot tested with an insulation of 2000V between primary and secondary windings and 1500V between the primary / secondary windings and the core.

Agency File:

UL: File E53148, UL 506, Class B General Purpose Transformer,
cUL: File E53148, UL 506, Class B General Purpose Transformer, Canadian Use



Dimensions:


A	B	C	D	E	F
2.500	2.00	1.062	0.267	0.500	2.00

Units: In inches

Weight: 11.0 oz

Pin Dimension: .020 x .041 in

Schematic:



RoHS Compliance: As of manufacturing date February 2005, all standard products meet the requirements of 2011/65/EU, known as the RoHS initiative.

* Upon printing, this document is considered "uncontrolled". Please contact Triad Magnetics' website for the most current version.

