


4

3

2

1

LOC	DIST	REVISIONS				
BD	39	P	LTR	DESCRIPTION	DATE	APVD
			H	0G3B-0317-03	24APR03	TK
			H1	REVISED PER ECO-09-020689	28AUG09	KK



1.

WIRE RANGE 18-14 AWG.
2.

INSULATION RANGE 2.03-3.43[.080-.135] DIA.
- 3

0.76μm [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA,
1.27μm [.000050] MIN TIN-LEAD IN LOCALIZED TIN-LEAD PLATE AREA,
BOTH OVER 1.27μm [.000050] MIN NICKEL.
- 4


TIN PLATED.
- 5

GOLD PLATING PER MIL-G-45204, TIN PER MIL-T-10727
AND NICKEL PER QQ-N-290.
- 6

0.76μm [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA,
1.27μm [.000050] MIN TIN IN LOCALIZED TIN PLATE AREA,
BOTH OVER 1.27μm [.000050] MIN NICKEL.
- 7

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

7	OBSOLETE	66577-7	6	66587-4
		66577-4	3	66587-2
		66577-2	4	66587-1
		STRIP REF	FINISH	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D.HARDY 06/15/94	 Tyco Electronics Corporation Harrisburg, PA 17105			
DIMENSIONS: INCHES		CHK R.STONE 06/22/94	NAME CONTACT, PIN, LOOSE PIECE, TYPE VI, MULTIMATE			
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.13 [.005] 3 PLC ± - 4 PLC ± - ANGLES ± -	APVD G.STEINMAUER 06/27/94				
		PRODUCT SPEC —				
		APPLICATION SPEC —				
		WEIGHT —				
MATERIAL BRS PER MIL-C-50	FINISH SEE TABLE	SIZE A3		CAGE CODE 00779	DRAWING NO C-66587	RESTRICTED TO —
CUSTOMER DRAWING			SCALE 6:1	SHEET 1	OF 1	REV H1