








NOTES:

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: 0.0=±0.4
0.00=±0.25
3. TERM. NOS. FOR REF. ONLY
4. ACTUATION FORCE: 130±40gf
5. TRAVEL TO MAKE: 0.3mm +0.4/-0.0
6. RATING: 30mA, @12V DC
7. CONTACT RESISTANCE: 50 milli-ohms typical
8. DIELECTRIC STRENGTH: 300V RMS min at sea level.
9. ELECTRICAL LIFE CYCLE: 1,000,000 make & break cycles at full load.
10. DESIGNATE MAJOR DIMENSIONS
11. 2002/95/EC (ROHS) COMPLIANT



RECOMMEND P.C.B. LAYOUT



CIRCUIT: SPST

CONTACT CONFIGURATION

D		18193	BUTTON LENGTH TOLERANCE CHG.	7/31/08	BLR
C		15472	REMOVED WASHABLE FROM DESC.	10/28/05	C
B		10088	REVISED & REDRAWN	1/27/99	
REV.		ECN No.	DESCRIPTION	DATE	CHKD
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED					
SCALE		DATE		DR	
5:1		7/31/08		BLR	
TITLE		DATE		DWG	
GS 10.00 F130 QP		L600001		REV	
D		DATE		REV	
7/31/08		L600001		D	