



M24758/7 Conduit-to-Stuffing Tube Fitting**M24758/7-04-B-A**

Basic Part No. _____
Conduit Size Code _____
Stuffing Tube Size Code _____

Material Designator:
A = Aluminum
B = Brass
C = CRES 316



1. The M24758/7 adapter couples MIL-S-24235/9 through MIL-S-24235/17 stuffing tubes to M24758/1 conduit.
2. Any combination of conduit and stuffing tube sizes may be ordered by identifying the appropriate conduit size and stuffing tube size in the part number configuration.
3. Metric dimensions (mm) are indicated in parentheses.
4. For complete dimensions see applicable Military Specification.

M24758/7 Conduit-to-Stuffing Tube Fitting



Conduit
Systems

TABLE I

Conduit Size Code	L Cone Length		M Dia (Maximum)
	±.06	(15.2)	
02	.750	(19.1)	.930 (23.6)
03	.750	(19.1)	1.120 (28.4)
04	.750	(19.1)	1.250 (31.8)
05	.750	(19.1)	1.430 (36.3)
06	.750	(19.1)	1.620 (41.1)
08	1.000	(25.4)	1.810 (46.0)
10	1.000	(25.4)	2.180 (55.4)
12	1.000	(25.4)	2.560 (65.0)
16	1.000	(25.4)	3.060 (77.7)
20	1.000	(25.4)	3.680 (93.5)
24	1.000	(25.4)	4.380 (111.3)

TABLE II

MIL-S-24235		A				P				
Stuffing Tube Size Code	Thread (Class 2A)	A	H		J		Dim		Q	
		Dia	±.02	(.5)	±.02	(.5)	(Minimum)	±.02	(.5)	
A	0.875 - 12 UN	.406 (10.3)	1.063	(27.0)	.188	(4.8)	1.031	(26.2)	.188	(4.8)
B	1.000 - 12 UN	.515 (13.1)	1.063	(27.0)	.188	(4.8)	1.125	(28.6)	.188	(4.8)
C	1.125 - 12 UN	.640 (16.3)	1.063	(27.0)	.188	(4.8)	1.250	(31.8)	.188	(4.8)
D	1.250 - 12 UN	.750 (19.1)	1.063	(27.0)	.188	(4.8)	1.375	(34.9)	.188	(4.8)
E	1.250 - 12 UN	.812 (20.6)	1.063	(27.0)	.188	(4.8)	1.375	(34.9)	.188	(4.8)
F	1.313- 12 UN	.843 (21.4)	1.188	(30.2)	.188	(4.8)	1.438	(36.5)	.188	(4.8)
G	1.500 - 12 UN	.935 (23.7)	1.188	(30.2)	.188	(4.8)	1.656	(42.1)	.188	(4.8)
J	1.625 - 12 UN	1.062 (27.0)	1.188	(30.2)	.188	(4.8)	1.781	(45.2)	.188	(4.8)
K	1.750 - 12 UN	1.171 (29.7)	1.500	(38.1)	.188	(4.8)	1.875	(47.6)	.188	(4.8)
L	1.813 - 12 UN	1.265 (32.1)	1.500	(38.1)	.188	(4.8)	1.938	(49.2)	.188	(4.8)
M	2.000 - 12 UN	1.406 (35.7)	1.500	(38.1)	.250	(6.4)	2.188	(55.6)	.188	(4.8)
N	2.063 - 12 UN	1.515 (38.5)	1.563	(39.7)	.250	(6.4)	2.250	(57.2)	.188	(4.8)
P	2.188 - 12 UN	1.625 (41.3)	1.563	(39.7)	.250	(6.4)	2.344	(59.5)	.188	(4.8)
R	2.313 - 12 UN	1.750 (44.5)	1.563	(39.7)	.250	(6.4)	2.469	(62.7)	.188	(4.8)
S	2.688 - 12 UN	1.875 (47.6)	2.188	(55.6)	.313	(8.0)	2.813	(71.5)	.250	(6.4)
T	2.875 - 12 UN	2.062 (52.4)	2.188	(55.6)	.313	(8.0)	2.969	(75.4)	.250	(6.4)
V	3.000 - 12 UN	2.187 (55.5)	2.188	(55.6)	.313	(8.0)	3.094	(78.6)	.250	(6.4)
W	3.125 - 12 UN	2.312 (58.7)	2.188	(55.6)	.313	(8.0)	3.281	(83.3)	.250	(6.4)
X	3.250 - 12 UN	2.500 (63.5)	2.188	(55.6)	.313	(8.0)	3.438	(87.3)	.250	(6.4)
Y	3.375 - 12 UN	2.609 (66.3)	2.188	(55.6)	.313	(8.0)	3.563	(90.5)	.250	(6.4)
Z	3.563 - 12 UN	2.781 (70.6)	2.188	(55.6)	.313	(8.0)	3.750	(95.3)	.250	(6.4)
AA	3.750 - 12 UN	2.875 (73.0)	3.125	(79.4)	.438	(11.1)	3.875	(98.4)	.250	(6.4)
BB	4.000 - 12 UN	3.157 (80.2)	3.125	(79.4)	.438	(11.1)	4.125	(104.8)	.250	(6.4)