


[Home](#) > [Search Tools](#) > [Part Number](#)

Part Number Search

You Searched For:

Note: Data provided here are offered in good faith and are as reliable and accurate as possible. However, they do not form part of any contract of supply or purchase unless specifically confirmed in writing by an authorized representative of ITT. All information and images shown are the property of ITT ICS and are not to be reproduced in any form without direct authorization from ITT ICS.

ITT ICS strongly recommends that you contact your local ITT Sales Office for confirmation of all the details you obtain through these Web pages. Please be aware that data may change at any time and without notice. For a listing of Sales Offices, local sales support, and authorized distributors please use the "Global Sales Locator" located either to the right of this data or at the top of every page.

[Sales Support](#)
[Product Overview](#)
[Stock Check](#)
[Product Home](#)

Our Descriptive Part Number: 0308612010

Our Global Manufacturing Part Number: 030-8612-010

	YES	RoHS compliant =	material restrictions of lead, cadmium, hexavalent chromium, mercury, poly bromated biphenyl ether (PBB) and poly bromide diphenyl ether (PBDE) according to directive 2002/95/EC
	NO	RoHS compatible =	Compatible with lead free soldering process

Product Datasheet	
Product Group	VG/CA-Bayonet
Component	Contact
Contact Gender	Pin
Termination Type	Crimp
Contact Size	60/100/8
Wire Range mm ²	2,00-3,00
Wire Size	14-12 AWG
Contact Plating	Silver
Dimension D1	Ø3,60 -0,05 (.142 -.002)
Dimension D4	Ø6,25 -0,15 (.246 -.006)
Dimension D6	Ø2,50 +0,05 (.098 +.002)
Dimension D7	Ø6,80 -0,10 (.268 -.004)
Dimension L1	39,60 ±0,15 (1.559 ±.006)
Dimension L3	6,35 ±0,50 (.250 ±.020)
Footnote	Dimensions are shown in mm (inch). Dimensions subject to change.
For more information	Contact Cannon Sales Department.