




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	E	REVISED PER ECO-16-017894	26APR2017	PHM	CT







SECTION X-X



P.C. BOARD LAYOUT (CONNECTOR SIDE)

- ① AMP, AMP PART NO. AND DATE CODE MARKED IN THIS APPROXIMATE AREA.
- ② HOUSING MATERIAL: LIQUID CRYSTAL POLYMER PER MIL-M-24519, GLCP-30F; COLOR: GRAY.
- ③ CONTACT: MATERIAL = PHOS BRONZE
- ④ PLATED .000030 GOLD IN THE CONTACT AREA, .000100 MIN TIN LEAD ON THE TAILS, ALL OVER .000050 NICKEL UNDER PLATE.
- ⑤ MICRO-MINATURE COAX CONTACT PER AMP DATA SHEET 80-600, PC BOARD MOUNTED CONTACTS MUST BE MATED BEFORE SOLDERING.
6. GROUP "A" INSPECTION PER MIL-C-55302 PERFORMED.
- ⑦ NUMBERS INDICATING END POSITIONS MARKED THIS SIDE ONLY.
- ⑧ ALIGNMENT RING MUST BE FLUSH TO BELOW MATING FACE.
9. MEETS SEALING EFFECTIVENESS TEST REQUIREMENT.

.700	[17.78]	.850	[21.59]	17	1.425	[36.20]	1.715	[43.56]	1	36	449874-1
E		D		C	B		A		NUMBER OF COAX POS.	NUMBER OF BOX POS.	PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.									DWN T. ALEXANDER 4-5-94 CHK D. GUTTER 4-12-94 APVD D. GUTTER 4-12-94 PRODUCT SPEC APPLICATION SPEC WEIGHT CUSTOMER DRAWING		
DIMENSIONS: INCHES  MATERIAL				TOLERANCES, UNLESS OTHERWISE SPECIFIED: 0 P/LC ± - 1 P/LC ± - 3 P/LC ± - 4 P/LC ± - ANGLES ± - FINISH -					 TE Connectivity RECEPTACLE ASSEMBLY, MINI-BOX W/ ONE COAX PORT, AND LOW FORCE CONTACTS SPECIAL		
 MATERIAL				TOLERANCES, UNLESS OTHERWISE SPECIFIED: 0 P/LC ± - 1 P/LC ± - 3 P/LC ± - 4 P/LC ± - ANGLES ± - FINISH -					NAME SIZE CASE CODE DRAWING NO RESTRICTED TO A1 00779 C=449874 -		
 MATERIAL				TOLERANCES, UNLESS OTHERWISE SPECIFIED: 0 P/LC ± - 1 P/LC ± - 3 P/LC ± - 4 P/LC ± - ANGLES ± - FINISH -					NAME SIZE CASE CODE DRAWING NO RESTRICTED TO A1 00779 C=449874 -		
 MATERIAL				TOLERANCES, UNLESS OTHERWISE SPECIFIED: 0 P/LC ± - 1 P/LC ± - 3 P/LC ± - 4 P/LC ± - ANGLES ± - FINISH -					NAME SIZE CASE CODE DRAWING NO RESTRICTED TO A1 00779 C=449874 -		