



(1,27 mm) .050"

FW-10-04-L-D-440-150

FW-40-02-F-D-425-075

FW-20-02-F-D-200-140

FW-TH SERIES

# THROUGH-HOLE MICRO BOARD STACKER

## SPECIFICATIONS

For complete specifications see [www.samtec.com?FW-TH](http://www.samtec.com?FW-TH)

**Insulator Material:**  
Black Liquid Crystal Polymer  
**Terminal Material:**  
Phosphor Bronze  
**Plating:**  
Sn or Au over  
50µ" (1,27 µm) Ni  
**Operating Temp Range:**  
-55°C to +125°C  
**RoHS Compliant:**  
Yes

**Processing:**  
Lead-Free Solderable:  
Yes

Mates with:  
CLP, FFSD, FLE

## RECOGNITIONS

For complete scope of recognitions see [www.samtec.com/quality](http://www.samtec.com/quality)




Low profile or  
skyscraper styles

(1,27 mm)  
.050" pitch

Variable  
board spacing

## ALSO AVAILABLE (MOQ Required)

- Smaller stack heights  
Contact Samtec.



**Note:** For added mechanical stability, Samtec recommends mechanical board spacers be used in applications with gold or selective gold plated connectors. Contact [ipg@samtec.com](mailto:ipg@samtec.com) for more information.

**Note:** This Series is non-standard, non-returnable.