








No. of pos.	A -0,76	B -0,25	C	D -0,3
9	31,19	16,46	25,00 ^{+0.12} / _{-0.10}	6,12
15	39,52	24,79	33,30 ^{+0.15}	6,12
25	53,42	38,50	47,04 ± 0.13	5,99
37	69,70	54,96	63,50 ^{+0.13} / _{-0.11}	5,99

NOTES:

- METALSHIELDS: COPPER ALLOY; min. 315µin TIN over 40-80µin NICKEL
- TPE ETHYLENE PROPYLENE THERMOPLASTIC RUBBER SEAL
- IP RATING: THE WATER RESISTANT CAP MUST BE MOUNTED PROPERLY TO THE MATING CONNECTOR FOR IP 67
- THREADED INSERT: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
- COLLAR: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
- JACKSCREW: STAINLESS STEEL 1.4305
- WIRE ROPE: STAINLESS STEEL 1.4401
- RETAINING WASHER: STAINLESS STEEL 1.4122
- TERMINAL RING: UNINSULATED, COPPER ALLOY; min. 200µinTIN over 80µin NICKEL
- MAXIMUM TORQUE VALUE FOR THREAD: 6in.LB
- CONNECTOR IS PART MARKED: **PART NO. CONEC ABC**

Directive 2002/95/EC
„RoHS“
Compliant

©

Part No. for plug connector		
No. of pos.	UNC 4-40	M 3
9	15-000110	15-000160
15	15-000120	15-000170
25	15-000130	15-000180
37	15-000140	15-000190

APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND

				tolerance		dim. in mm	
				date	name		
				drawn	02.05.08	Sonnenberg	
				appd.	02.05.08	Fischer	
				norm			
1 x c	Ä 3182	10.11.08	Petker	d-old			
1 x b	Ä 3023	28.05.08	Petker				
a	Origin						
rev.	description	date	name				

CONEC

scale:	2:1 (5:1)		
material:	SEE NOTES		
title:	WATER RESISTANT SCREEN CAP 9-37pos. FOR PLUG CONNECTOR with threaded insert, jackscrew and wire rope		
dwg no:	Inventor 10	DIN- A3	
	15K1A218		sh: 1
part no:	see table		