

10

9

8

7

6

5

4

3

2

1

F


E

D



C

B

A




△ケーブルクランプ部



NOTE.

1. 材質及び処理 : ステンレス鋼 (H=2)
MATERIAL AND FINISH. STAINLESS STEEL
2. 推奨使用ケーブル外径 : 4.3±0.2
CABLE O.D
3. 推奨ケーブルクランプカシメ外径 :
SHIELD CAULKING O.D



4. 本製品のケーブルクランプ部のグラッドはフレームグラッドを目的としており、シグナルグラッドとしての機能は保証致しません。

5. メッキ仕様 : ニッケルメッキ 1~3 μm
PLATING SPEC NICKEL

59744-1411	59744-1411
MATERIAL NO.	MODEL NO.

RELEASED EC NO.: J2010-2025 DRAWN: NAKATA CHKD: JMARONEY APPR: MYAGI REV: 0	DESCRIPTION 2010/04/08 2010/04/09 2010/04/13	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	
		10 UNDER	± 0.2	DRAWN BY	DATE	TITLE 0.5 I/O CONN REC 14PIN SHIELD			
		10 OVER 30 UNDER	± 0.25	CHECKED BY	DATE				
		30 OVER	± 0.3	JMARONEY	2010/04/09				
		APPROVED BY	DATE	MOLEX MOLEX INCORPORATED					
	MYAGI	2010/04/13							
	ANGULAR ±3 °		MATERIAL NO.		DOCUMENT NO.		SHEET NO.		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		SD-59744-002		1 OF 1			
		SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						

9

8

7

6

5

4

3

2