




- ⬢ IP68 rating tested at 1.054kg/sq cm (15lb/sq in) 10m depth for 2 weeks
- ⬢ IP69K, Tested in accordance with DIN 40050/Part 9 IP6k9k
- ⬢ 2 and 3 pole - 8A, 250V rating
- ⬢ 4, 6 and 8 pole - 5A, 125V rating
- ⬢ 10 and 12 pole - 1A, 50V rating
- ⬢ 2.5mm contact engagement for electrical integrity 'Scoop proof' contacts
- ⬢ Contact inserts are part of body moulding
- ⬢ Cable range from 3 to 7mm
- ⬢ Overall length (flex + flex in-line) 80mm
- ⬢ Gold plated contacts
- ⬢ Diameter over coupling ring 19.1mm
- ⬢ Pre-wired, overmoulded cable assemblies
- ⬢ Flex, Flex In-Line, Front Panel, Rear Panel and PCB mounting body styles
- ⬢ Plug and Socket versions in all body styles
- ⬢ Flame Retardant moulding material - Polyamide UL94-V0
- ⬢ Contacts supplied separately (except PCB versions)
- ⬢ Sealing caps available to maintain IP68 rating
- ⬢ Secure sealing system
- ⬢ Crimp and solder contacts
- ⬢ PCB mounting connector supplied with contacts pre-loaded
- ⬢ Front and rear panel mounting panel connectors
- ⬢ CCC, UL, CSA and VDE approvals
- ⬢ EN60068-2-52 Test Kb Salt Mist (Cyclic) Marine Severity Level 1
- ⬢ Smart options available with EEPROM memory chip

Flex Cable Connector



PX0410

- Mates with Flex In-line or Panel mounting versions PX0401, PX0411, PX0412 & PX0413
- Pin or socket
- 2, 3, 4, 6, 8, 10 or 12 pole
- Screw locking ring
- Contacts supplied separately




Inline Flex Cable Connector



PX0411

- Mates with Flex Cable connectors PX0400, PX0402 & PX0410
- Pin or socket
- 2, 3, 4, 6, 8, 10 or 12 pole
- For in-line cable connection
- Contacts supplied separately




Pre Wired Flex Cable Connector



PX0400

- Overmoulded Flex connector for pre-wired cable assemblies
- Pin or socket
- Cable range 2.5 -9.0mm o/d
- 2, 3, 4, 6, 8, 10 or 12 pole
- Mates with PX0401 & PX0411 Flex In-Line connectors and PX0412 & PX0413 panel mounting connectors




Smart Connector



PXS4 XX

- Overmoulded pre-wired sealed connector
- 4, 6, 8, 10, 12 pole
- Embedded memory chip through 1 wire EEPROM
- Mates with PX0401 & PX0411 Flex In-Line connectors and PX0412 & PX0413 panel mounting connectors




Pre Wired Flex Cable Connector



PX0402

- Right-angled overmoulded Flex connector for pre-wired cable assemblies
- Pin or socket
- Cable range 2.5 -9.0mm o/d
- 2, 3, 4, 6, 8, 10 or 12 pole
- Mates with PX0401 & PX0411 Flex In-Line connectors and PX0412 & PX0413 panel mounting connectors




Pre Wired Inline Flex Connector



PX0401

- Overmoulded Flex connector for pre-wired cable assemblies
- Pin or socket
- Cable range 2.5 -9.0mm o/d
- 2, 3, 4, 6, 8, 10 or 12 pole
- Mates with PX0400, PX0402 & PX0410 Flex connectors




Front Panel Mounting Connector



PX0412

- Mates with Flex Cable connectors PX0410, PX0400 & PX0402
- Front Panel mounting
- Single hole fixing
- Contacts supplied separately
- 2, 3, 4, 6, 8, 10 or 12 pole




Rear Panel Mounting Connector



PX0413

- Mates with Flex Cable connector PX0410, PX0400 & PX0402
- Rear Panel mounting
- Single hole fixing
- Contacts supplied separately
- 2, 3, 4, 6, 8, 10 or 12 pole




PCB Mounting Connector



PX0413

- Mates with Flex Cable connector PX0410, PX0400 & PX0402
- PCB Rear Panel mounting
- Straight PC spills
- Supplied with pre-loaded gold plated contacts
- 2, 3, 4, 6, 8, 10 or 12 pole



Sealing Caps and Accessories



PX0480 PX0480/1 PX0481 PX0484

- Maintains IP68 Rating of Unmated Connectors
- PX0480: Fits PX0412 (panel mounting)
- PX0480/1: Fits PX0401 & PX0411 (flex in-line)
- PX0481: Fits PX0400, PX0402 & PX0410 (flex connector)
- PX0484: Fits PX0413 (PCB and rear panel mount)

Gland Packs

Part No	Description
PX0482	Pack of 4 pairs cable glands and collets to suit cables from 3.0 to 5.0mm diameter.
PX0483	Pack of 4 pairs cable glands and collets to suit cables from 5.0 to 7.0mm diameter.

Crimp Contacts

Pole	Current Rating	Pin	Socket	Pack Qty	Cable Acceptance (dia)
2, 3	8A	SA3350	SA3349	10	20 - 24 AWG
4, 6, 8	5A	SA3348	SA3347	10	22 - 26 AWG
10, 12	1A	SA3180	SA3179	10	24 - 28 AWG

Solder Contacts

Pole	Current Rating	Pin	Socket	Pack Qty	Cable Acceptance (dia)
2, 3	8A	SA3350/1	SA3349/1	10	20 - 24 AWG
4, 6, 8	5A	SA3348/1	SA3347/1	10	22 - 26 AWG
10, 12	1A	SA3180/1	SA3179/1	10	24 - 28 AWG

Insertion / Extraction

	Poles	Contact Rating	Colour	Part No
Insertion/Extraction Tool	2,3	8A	Blue	13027/2
Insertion/Extraction Tool	4,6,8	5A	Red	13027/1
Insertion/Extraction Tool	10,12	1A	Green	13027


Crimp tools

	Poles	Contact Rating	Colour	Part No
Positioner	2,3	8A	Blue	14025/8AMP
Positioner	4,6,8	5A	Red	14025/5AMP
Positioner	10,12	1A	Green	14025/1AMP
8 Indent Crimp Tool for use with positioners				14025

PX0413 PCB Contact Layout


Sockets

Contact numbers viewed from rear of panel



Plugs

Contact numbers viewed from rear of panel



2 pole
(8 Amp)



3 pole
(8 Amp)



4 pole
(5 Amp)



6 pole
(5 Amp)



8 pole
(5 Amp)



10 pole
(1 Amp)



12 pole
(1 Amp)

Electrical:

No. Poles:	2, 3	4, 6, 8	10, 12
Current Rating:	8A	5A	1A
Voltage Rating (ac/dc):	250Vac/dc	125Vac/dc	50Vacdc
Contact Resistance:	<5mΩ		
Insulation Resistance:	>10 ⁹ MΩ (@ 500V d.c.)		
AC Breakdown voltage:	2.5kV		

Operating Temperature:	
Flex and panel types	-40°C to +80°C
Overmoulded	-20°C to +60°C

Approvals:

 UL	E214972
 CSA	1273303
 VDE	40002226
 CCC	2011010203500398 – 1 Amp Rated
	2011010203500399 – 5 Amp Rated
	2011010203500400 – 8 Amp Rated
	Overmoulded cable assemblies approvals to customer requirements.

Material:

Flex and panel types:	
Body Mouldings:	Polyamide
Flammability Rating:	UL94V-0
UV Resistance:	To EN 50021:1999
Overmoulded types:	
Body Mouldings:	Polyurethane
Flammability Rating:	UL94V-HB
Contacts:	Copper alloy, Gold plated
O Rings:	Nitrile
Panel Sealing O Ring:	Nitrile
	Compliant

Mechanical:

Sealing:	IP69K, Tested in accordance with DIN 40050/Part 9 IP6k9k
	IP68, EN60529:1992+A2:2013 tested @ 1.054kg/sq cm (15lb/sq in) 10m depth for 2 weeks
Salt Mist:	EN60068-2-52 Test Kb Salt Mist (Cyclic) Marine Severity Level 1
Cable Acceptance:	3.0 - 7.0mm
Contact Accommodation:	2, 3 pole, 20 - 24 AWG 4, 6, 8 pole, 22 - 26 AWG 10, 12 pole, 24 - 28 AWG
Termination:	Crimp, solder and PCB
Insertion/Withdrawal Force:	
No. poles:	2 3 4 6 8 10 12
Insertion Force (typ):	19N 25N 27N 27N 28N 55N 62N
Withdrawal Force (typ):	12N 17N 17N 21N 22N 25N 29N
Tightening Torques:	
Panel mount (PX0412)	
Rear fixing nut:	1.0-1.1Nm (9lbf.in.)
Panel mount (PX0413)	
Front fixing nut:	1.0-1.1Nm (9lbf.in.)
Cable Retention force:	
3.0mm dia	60N
4.0 to 7.0mm dia	80N
Rear panel thread PX0412:	M16x1.5
Panel thread PX0413:	18.97x26TPI Whitworth form to BS84 med fit

Dimensions:

Overall dimensions of connectors when mated together

Flex + Flex In-Line	80mm
Dia. over coupling ring	19.1mm

Dia. over coupling ring

Smart Connector EEPROM:

1024 - Bit Memory
 1 - Wire
 Can be Write Protected
 Manufacturer - Maxim Intergrated
 Part Number - 0S2431

Standard:

PX04 xx	/	XX	/	X	/	XXXX
Body Styles PX0410 = Flex body PX0411 = Flex in-line body PX0412 = Front panel mounting body PX0413 = Rear panel/PCB mounting body		Number Contacts 02 = 2 pole, 03 = 3 pole, 04 = 4 pole, 06 = 6 pole, 08 = 8 pole, 10 = 10 pole, 12 = 12 pole		Contact Type P = Pin, S = Socket		For PX0410 and PX0411 cable connectors - Cable Entry Size: 3035 = 3.0 - 3.5mm (Light Grey) 3540 = 3.5 - 4.0mm (Grey) 4045 = 4.0 - 4.5mm (Green) 4550 = 4.5 - 5.0mm (Red) 5055 = 5.0 - 5.5mm (Yellow) 5560 = 5.5 - 6.0mm (Blue) 6065 = 6.0 - 6.5mm (White) 6570 = 6.5 - 7.0mm (Black) Cable gland and collet supplied in colour coded pairs. For PX0413 PCB/Rear Panel Mount: PC = Pre-loaded PC pins Blank = no pins supplied For PX0412 Front Panel Mount: Suffix not required - leave blank

Examples:

PX0410/10S/4045 = Flex cable connector, 10 socket contacts with gland and collet for cables between 4.0 and 4.5mm diameter (supplied less contacts).
PX0412/08P = Front panel mounting connector, 8 pin contacts (supplied less contacts).
PX0413/06P = Rear panel mounting connector, for 6 pin contacts (supplied less contacts).
PX0413/04P/PC = Rear panel/PCB connector, 4 pin contacts, PCB mounting (supplied with contacts loaded).

Smart:

PXS4xx	/	XX	/	XX	/	X
Body Styles PXS410 = Flex body		Cable length 02 = 2m 03 = 3m 05 = 5m 10 = 10m		Number of Contacts 04 = 4 poles 06 = 6 pole 08 = 8 pole 10 = 10 pole 12 = 12 pole		Contact Type P = Pin S = Socket

Examples:

PXS410/02/04/P = Smart flex cable connector, 2M cable to free end, 4 pin contact

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Bulgin:

[SA3349](#) [SA3350](#) [PX0412/10P](#) [PX0412/10S](#) [PX0412/06P](#) [PX0412/06S](#) [SA3349/1](#) [SA3347/1](#) [PX0413/10P/PC](#)
[PX0412/04S](#) [PX0412/03P](#) [PX0412/08P](#) [PX0412/08S](#) [PX0412/02P](#) [PX0412/03S](#) [PX0412/02S](#) [PX0412/04P](#)
[PX0411/04P/4550](#) [PX0411/08P/6065](#) [PX0411/08S/6065](#) [PX0411/04S/4550](#) [PX0411/02P/5560](#) [PX0411/03P/5560](#)
[PX0411/03S/5560](#) [PX0411/02S/5560](#) [PX0410/12P/6065](#) [PX0410/12S/6065](#) [SA3350/1](#) [PX0412/12S](#) [PX0412/12P](#)
[SA3348/1](#) [PX0413/04P/PC](#) [PX0413/06P/PC](#) [PX0484](#) [PX0483](#) [PX0482](#) [PX0481](#) [PX0480](#) [PX0413/08P/PC](#)
[PX0413/06S/PC](#) [PX0480/1](#) [PX0413/04S/PC](#) [PX0413/12S/PC](#) [PX0413/10S/PC](#) [SA3348](#) [SA3347](#) [PX0410/03P/5560](#)
[PX0410/08S/6065](#) [PX0410/03S/5560](#) [PX0410/08P/6065](#) [PX0410/04S/4550](#) [PX0410/02S/5560](#) [PX0410/04P/4550](#)
[PX0410/02P/5560](#) [PX0413/08S/PC](#) [PX0411/12S/6065](#) [PX0411/12P/6065](#) [PX0413/12P/PC](#) [PX0410/03S/6065](#)
[PX0410/02P/3035](#) [PX0410/02P/3540](#) [PX0410/02P/4045](#) [PX0410/02P/4550](#) [PX0410/02P/5055](#) [PX0410/02P/6065](#)
[PX0410/02P/6570](#) [PX0410/02S/3035](#) [PX0410/02S/3540](#) [PX0410/02S/4045](#) [PX0410/02S/4550](#) [PX0410/02S/5055](#)
[PX0410/02S/6065](#) [PX0410/02S/6570](#) [PX0410/03P/3035](#) [PX0410/03P/3540](#) [PX0410/03P/4045](#) [PX0410/03P/4550](#)
[PX0410/03P/5055](#) [PX0410/03P/6065](#) [PX0410/03P/6570](#) [PX0410/03S/3035](#) [PX0410/03S/3540](#) [PX0410/03S/4045](#)
[PX0410/03S/4550](#) [PX0410/03S/5055](#) [PX0410/03S/6570](#) [PX0410/04P/3035](#) [PX0410/04P/3540](#) [PX0410/04P/4045](#)
[PX0410/04P/5055](#) [PX0410/04P/5560](#) [PX0410/04P/6065](#) [PX0410/04P/6570](#) [PX0410/04S/3035](#) [PX0410/04S/3540](#)
[PX0410/04S/4045](#) [PX0410/04S/5055](#) [PX0410/04S/5560](#) [PX0410/04S/6065](#) [PX0410/04S/6570](#)