

TPE series characteristics list

Size code	Part number	Rated voltage (V)	Rated temperature (°C)	Rated capacitance (μF)	Category voltage (V)	Category temperature (°C)	DF (% max)	LC (μA) max/5min.	ESR (mΩmax) 100kHz/20°C	Maximum allowable ripple current (mA rms) 100kHz※1	MSL Reflow temp. ≤ 260°C Reflow temp. ≤ 250°C	
B2	10TPE47MAZB	10	85	47	8.0	105	8.0	47.0	35	1400	3	3
	8TPE100MAZB	8.0	85	100	6.3	105	8.0	80.0	35	1400	3	3
	6TPE220MAZB	6.3	85	220	5.0	105	10	138.6	35	1400	3	3
	6TPE220MAPB※2	6.3	85	220	5.0	105	10	138.6	25	1400	3	3
	6TPE150MAZB	6.3	85	150	5.0	105	8.0	94.5	35	1400	3	3
	6TPE150MAPB	6.3	85	150	5.0	105	8.0	94.5	25	1600	3	3
	6TPE120MAZB	6.3	85	120	5.0	105	8.0	75.6	35	1400	3	3
	6TPE100MPB	6.3	105	100	6.3	105	8.0	63.0	25	1600	3	3
	6TPE100MAZB	6.3	85	100	5.0	105	8.0	63.0	35	1400	3	3
	4TPE220MAZB	4.0	85	220	3.2	105	8.0	88.0	35	1400	3	3
	4TPE150MAZB	4.0	85	150	3.2	105	8.0	60.0	35	1400	3	3
	4TPE100MZB	4.0	105	100	4.0	105	8.0	40.0	35	1400	3	3
	2R5TPE330MAZB	2.5	85	330	2.0	105	8.0	82.5	35	1400	3	3
	ETPE330MAFB※2	2.5	85	330	2.0	105	8.0	165.0	15	2700	3	3
	ETPE330MA9GB※2	2.5	85	330	2.0	105	8.0	165.0	9/300kHz	3200	3	3
	2R5TPE220MZB	2.5	105	220	2.5	105	8.0	55.0	35	1400	3	3
	2R5TPE220MLB	2.5	105	220	2.5	105	8.0	55.0	21	1700	3	3
	2R5TPE220MFGB	2.5	105	220	2.5	105	8.0	110.0	15/300kHz	1800	3	3
	2R5TPE220MAZB	2.5	85	220	2.0	105	8.0	55.0	35	1400	3	3
	2R5TPE220MAPB	2.5	85	220	2.0	105	8.0	55.0	25	1600	3	3
	2R5TPE220MAFB	2.5	85	220	2.0	105	8.0	110.0	15	2000	3	3
	2TPE470MAJGB	2.0	85	470	1.8	105	10	188.0	11/300kHz	2300	3	3
	2TPE330MFB	2.0	105	330	2.0	105	8.0	132.0	15	2000	3	3
	2TPE330MAFB	2.0	85	330	1.8	105	8.0	132.0	15	2000	3	3
	2TPE330MADGB	2.0	85	330	1.8	105	8.0	132.0	13/300kHz	2000	3	3

※1 100k to 500kHz,45°C ※2 Under development

TPE series characteristics list

Size code	Part number	Rated voltage (V)	Rated temperature (°C)	Rated capacitance (μF)	Category voltage (V)	Category temperature (°C)	DF (% max)	LC (μA) max/5min.	ESR (mΩmax) 100kHz/20°C	Maximum allowable ripple current (mA rms) 100kHz※1	MSL	
											Reflow temp. ≤ 260°C	Reflow temp. ≤ 250°C
D15E	6TPE470MAZU	6.3	85	470	5.0	105	10	296.1	35	1700	3	2a
D2E	10TPE68M	10	105	68	10	105	10	68.0	25	2400	3	2a
	6TPE330MAP	6.3	85	330	5.0	105	10	207.9	25	2400	3	2a
	6TPE220MAP	6.3	85	220	5.0	105	10	138.6	25	2400	3	2a
	6TPE220M	6.3	105	220	6.3	105	10	138.6	25	2400	3	2a
	6TPE220MI	6.3	105	220	6.3	105	10	138.6	18	2800	3	2a
	6TPE150M	6.3	105	150	6.3	105	10	94.5	25	2400	3	2a
	6TPE150MI	6.3	105	150	6.3	105	10	94.5	18	2800	3	2a
	6TPE150MF	6.3	105	150	6.3	105	10	94.5	15	3100	3	2a
	6TPE100M	6.3	105	100	6.3	105	10	63.0	25	2400	3	2a
	6TPE100MI	6.3	105	100	6.3	105	10	63.0	18	2800	3	2a
	4TPE330M	4.0	105	330	4.0	105	10	132.0	25	2400	3	2a
	4TPE330MI	4.0	105	330	4.0	105	10	132.0	18	2800	3	2a
	4TPE220M	4.0	105	220	4.0	105	10	88.0	25	2400	3	2a
	4TPE220MI	4.0	105	220	4.0	105	10	88.0	18	2800	3	2a
	4TPE220MF	4.0	105	220	4.0	105	10	88.0	15	3100	3	2a
	4TPE150MI	4.0	105	150	4.0	105	10	60.0	18	2800	3	2a
	2R5TPE470MI	2.5	105	470	2.5	105	10	117.5	18	2800	3	2a
	2R5TPE470MF	2.5	105	470	2.5	105	10	117.5	15	3100	3	2a
	2R5TPE470MC	2.5	105	470	2.5	105	10	117.5	12	3500	3	2a
	2R5TPE470M9	2.5	105	470	2.5	105	10	117.5	9	3900	3	2a
	2R5TPE470M7	2.5	105	470	2.5	105	10	117.5	7	4400	3	2a
	2R5TPE330M	2.5	105	330	2.5	105	10	82.5	25	2400	3	2a
	2R5TPE330MI	2.5	105	330	2.5	105	10	82.5	18	2800	3	2a
	2R5TPE330MF	2.5	105	330	2.5	105	10	82.5	15	3100	3	2a
	2R5TPE330MC	2.5	105	330	2.5	105	10	82.5	12	3500	3	2a
	2R5TPE330M9	2.5	105	330	2.5	105	10	82.5	9	3900	3	2a
	2R5TPE330M7	2.5	105	330	2.5	105	10	82.5	7	4400	3	2a
	2R5TPE220M	2.5	105	220	2.5	105	10	55.0	25	2400	3	2a
	2R5TPE220MI	2.5	105	220	2.5	105	10	55.0	18	2800	3	2a
	2R5TPE220MF	2.5	105	220	2.5	105	10	55.0	15	3100	3	2a
	2R5TPE220M9	2.5	105	220	2.5	105	10	55.0	9	3900	3	2a
D3L	10TPE220ML	10	105	220	10	105	10	220.0	25	2400	—	2a
	10TPE220MIL	10	105	220	10	105	10	220.0	18	2800	—	2a
	6TPE330MAL	6.3	85	330	5.0	105	10	207.9	25	2400	3	2a
	6TPE330MA9EL	6.3	85	330	5.0	105	10	207.9	9/500kHz	3900	3	2a
	6TPE330ML	6.3	105	330	6.3	105	10	207.9	25	2400	3	2a
	6TPE330MIL	6.3	105	330	6.3	105	10	207.9	18	2800	3	2a
	6TPE330MFL	6.3	105	330	6.3	105	10	207.9	15	3100	3	2a
	4TPE470ML	4.0	105	470	4.0	105	10	188.0	25	2400	3	2a
	4TPE470MIL	4.0	105	470	4.0	105	10	188.0	18	2800	3	2a
	4TPE470MFL	4.0	105	470	4.0	105	10	188.0	15	3100	3	2a
	4TPE470MCL	4.0	105	470	4.0	105	10	188.0	12	3500	3	2a
	4TPE470MAL ※2	4.0	105	470	4.0	105	10	188.0	10	4400	3	2a
D4	2R5TPE680MFL	2.5	105	680	2.5	105	10	170.0	15	3100	3	2a
	2R5TPE680MCL	2.5	105	680	2.5	105	10	170.0	12	3500	3	2a
	10TPE330M	10	105	330	10	105	10	330.0	25	3000	—	2a
	6TPE680M	6.3	105	680	6.3	105	15	428.4	25	3000	3	2a
	6TPE680MI	6.3	105	680	6.3	105	15	428.4	18	3500	3	2a
	6TPE470M	6.3	105	470	6.3	105	15	296.1	25	3000	3	2a
	6TPE470MI	6.3	105	470	6.3	105	15	296.1	18	3500	3	2a
	6TPE330MAA	6.3	85	330	5.0	105	15	207.9	10	4400	3	2a
	2R5TPE1000MF	2.5	105	1000	2.5	105	15	250.0	15	3900	3	2a
	2R5TPE1500MF	2.5	105	1500	2.5	105	15	375.0	15	3900	—	2a
	2R5TPE1500MC	2.5	105	1500	2.5	105	15	375.0	12	4400	—	2a

※1 100k to 500kHz, 45°C

※2 Under development