

6.0×6.0mm TACT Switch (Radial)

SKHV Series

Advantage in excellent mounting efficiency. Ground terminal version is also available.

Power
Push
Slide
Rotary
Encoders

Jog Shuttle
Telephone hook

Detector

Vibration Sensors

Dual-in-line Package Type

Multi Control Devices

TACT


Sharp Feeling

Soft Feeling

Snap-in Type

Surface Mount Type

Radial Type



Car Use

Features

- Supplied with radial taping.
- Allows automatic insertion onto PC board with the radial auto insertion machine.

Applications

- For operating various electronic devices such as audio devices, office equipment, communication devices, TVs, video recorders, etc.

Products Line

Vertical Type

Products No.	Operating force	Operating direction	Travel (mm)	Rating (max.)	Operating life (5mA 5V DC)	Initial contact resistance	Stem color	Stem height	Drawing No.
SKHVBAD010	0.98N	Vertical	0.25	50mA 12V DC	1,000,000cycles	100m Ω max.	Black	h=4.3mm	1
SKHVBBD010	1.57N				500,000cycles		Dark gray		
SKHVBCD010	2.55N				200,000cycles		Red		
SKHVBDD010	0.98N				1,000,000cycles		Black	h=5mm	
SKHVBED010	1.57N				500,000cycles		Dark gray		
SKHVBFD010	2.55N				200,000cycles		Red		
SKHVCED010	5.10N				1,000,000cycles		Yellow	h=7mm	
SKHVBKD010	0.98N						Black		
SKHVBLD010	1.57N						Dark gray		
SKHVBMD010	2.55N				200,000cycles		Red	h=9.5mm	
SKHVBGD010	0.98N				1,000,000cycles		Black		
SKHVBHD010	1.57N				500,000cycles		Dark gray		
SKHVBJD010	2.55N				200,000cycles		Red		

With Ground Terminal Type

Products No.	Operating force	Operating direction	Travel (mm)	Rating (max.)	Operating life (5mA 5V DC)	Initial contact resistance	Stem color	Stem height	Drawing No.
SKHVPAD010	0.98N	Vertical	0.25	50mA 12V DC	1,000,000cycles	100m Ω max.	Black	h=4.3mm	2
SKHV PBD010	1.57N				500,000cycles		Dark gray		
SKHVPCD010	2.55N				200,000cycles		Red		
SKHV PDD010	0.98N				1,000,000cycles		Black	h=5mm	
SKHV PED010	1.57N				500,000cycles		Dark gray		
SKHV PFD010	2.55N				200,000cycles		Red		
SKHV PKD010	0.98N				1,000,000cycles		Black	h=7mm	
SKHVPLD010	1.57N				500,000cycles		Dark gray		
SKHV PMD010	2.55N				200,000cycles		Red		
SKHV PGD010	0.98N				1,000,000cycles		Black	h=9.5mm	
SKHV PHD010	1.57N				500,000cycles		Dark gray		
SKHV PJD010	2.55N				200,000cycles		Red		





For detailed specifications, see P.413

For soldering conditions, see P.414



For specifications for the taping package, see P.417

Dimensions

Unit : mm

No.	Style	PC board mounting hole dimensions (Viewed from switch mounting face)											
1	Vertical type 	<table><tr><th>h</th><th>A</th></tr><tr><td>4.3</td><td>3.5</td></tr><tr><td>5</td><td>3.5</td></tr><tr><td>7</td><td>3.3</td></tr><tr><td>9.5</td><td>3</td></tr></table>	h	A	4.3	3.5	5	3.5	7	3.3	9.5	3	
		h	A										
4.3	3.5												
5	3.5												
7	3.3												
9.5	3												
2	With ground terminal type 	<table><tr><th>h</th><th>A</th></tr><tr><td>4.3</td><td>3.5</td></tr><tr><td>5</td><td>3.5</td></tr><tr><td>7</td><td>3.3</td></tr><tr><td>9.5</td><td>3</td></tr></table>	h	A	4.3	3.5	5	3.5	7	3.3	9.5	3	
		h	A										
4.3	3.5												
5	3.5												
7	3.3												
9.5	3												

Circuit Diagram

Vertical type	With ground terminal type
	

Note

Using a 1.6mm thick PC board is recommended.

Power

Push

Slide

Rotary

Encoders

Jog Shuttle

Telephone -hook

Detector

Vibration Sensors

Dual-in-line Package Type

Multi Control Devices

TACT

Sharp Feeling

Soft Feeling

Snap-in Type

Surface Mount Type

Radial Type

Products Specifications

Series		Sharp feeling type	Soft feeling type
Items			
Operating temperature range		-20°C to +70°C	
		-30°C to +85°C SKRM / RW	-30°C to +80°C SKPG
		-30°C to +90°C SKRA / RG / RP	-40°C to +90°C SKPF / PL / PM/ PN
Rating (max.)		50mA 12V DC SKRP : 50mA 16V DC	5mA 12V DC SKPL/PM/PN : 50mA 16V DC
Rating (min.)		10 μ A 1V DC	
Electrical performance	Insulation resistance	100M Ω SKEY/PD : 50M Ω	
	Voltage proof	250V AC for 1 min. SKRB/RH/RM/RR/EY/PD : 100V AC for 1min.	
Durability	Vibration	10 to 55 to 10Hz/min., the amplitude is 1.5mm for all the frequencies, in the 3 direction of X, Y and Z for 2 hours respectively	
	Lifetime	Shall be in accordance with individual specifications.	
Environmental performance	Cold	-30 $\pm$ 2°C for 96h	
	Dry heat	80 $\pm$ 2°C for 96h	
	Damp heat	60 $\pm$ 2°C, 90 to 95%RH for 96h	

Power

Push

Slide

Rotary

Encoders

Jog Shuttle

Telephone hook

Detector

Vibration Sensors

Dual-in-line Package Type

Multi Control Devices

TACT

Note

We can raise the working temperature range for in-vehicle applications upon request. Contact us if you have any requirements of this kind.

Specifications of LED (SKHJ)

Color of light	Power dissipation P (mW)	Forward pulse peak current IFP (mA)	Forward current IFDC (mA)	Reverse voltage VR (V)	Forward voltage VF (V) IF=10mA	Reverse current IR (μ A) VR=4V	Peak emission wave length λ peak (nm) IF=10mA	Spectral line half width $\Delta \lambda$ (nm) IF=10mA	Luminous intensity IV (mcd) IF=10mA
Red	40	80	15	4	2.7 max. 2.05TYP	5 max.	700 TYP	100 TYP	0.4min. 1.0 TYP
Pure green					2.7 max. 2.0 TYP	10 max.	555 TYP	20 TYP	0.8min. 2.0 TYP
Amber							590 TYP	30 TYP	0.4min. 1.0 TYP
Orange (High brightness)				3			630 TYP	40 TYP	1.5min. 4.0 TYP
Green (High brightness)				4	2.7 max. 2.05TYP		565 TYP	30 TYP	2.0min. 5.0 TYP

Sharp Feeling

Soft Feeling

Snap-in Type

Surface Mount Type


Radial Type

Soldering Conditions

Condition for Reflow

Available for Surface Mount Type. (Except SKHM Series)

- 1. Heating method: Double heating method with infrared heater.
- 2. Temperature measurement: Thermocouple 0.1 to 0.2 ϕ CA (K) or CC (T) at soldering portion (copper foil surface) . A heat resisting tape should be used for fixed measurement.
- 3. Temperature profile



Notes

- 1. The condition mentioned above is the temperature on the mounting surface of a PC board. There are cases where the PC board's temperature greatly differs from that of the switch, depending on the PC board's material, size, thickness, etc. The above-stated conditions shall also apply to switch surface temperatures. (Except a part of Variety SKRM, SKRR Series)
- 2. Soldering conditions differ depending on reflow soldering machines. You are requested to verify the soldering conditions thoroughly beforehand.
- 3. Ask us for the specifications of lead-free products.

Conditions for Auto-dip

Available for Snap-in Type and Radial Type

Items	Condition
Flux built-up	Mounting surface should not be coated with flax
Preheating temperature	Ambient temperature of the soldered surface of PC board. 100°C max.
Preheating time	45s max.
Soldering temperature	255°C max.
Continuous dipping time	5s max.
Number of soldering	2times max.

Notes

- 1. Consult with us for TACT switch washing conditions.
- 2. Prevent flux penetration from the top side of the TACT switch.
- 3. Switch terminals and a PC board should not be coated with flux prior to soldering.
- 4. The second soldering should be done after the switch returns to normal temperature.
- 5. Use the flux with a specific gravity of at least 0.83. (MH-820V or CF220V by TAMURA Corporation, or their equivalents.)

Manual Soldering

Available for Manual Soldering Type

Items	Condition
Soldering temperature	350°C max.
Continuous soldering time	3s max.


Specification of Radial Taping Package

Taping Packaging for Auto-insertion

The SKHV, SKQC, SKQK, SKQN, SKQW, SKRC, SKRG, SKRS, SKPD and SKPL series are delivered with taping packaging.

Box Size

Unit : mm



Quantity Accommodated Per Box

Series	Qty / reel (pcs.) (Minimum packing unit)
SKHV SKQK	1,000
SKQW SKRS	700
SKQC	1,500
SKPD	800
SKRG	2,000
SKQN SKRC	900
SKPL	2,700

Power

Push

Slide

Rotary

Encoders

Jog
Shuttle

Telephone
-hook

Detector

Vibration
Sensors

Dual-in-line
Package Type

Multi Control
Devices

TACT

Sharp
Feeling

Soft
Feeling

Snap-in
Type

Surface
Mount Type

Radial
Type

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ALPS:

[SKHVBHD010](#) [SKHVBKD010](#) [SKHVBJD010](#) [SKHVBDD010](#) [SKHVBMD010](#) [SKHVBGD010](#) [SKHVBLD010](#)
[SKHVBFD010](#) [SKHVLKD010](#) [SKHVBBD010](#) [SKHVBED010](#) [SKHVBCD010](#) [SKHVBAD010](#) [SKHVLJD010](#)
[SKHVLHD010](#)