

V3-3019

M

DRAWING
NUMBER

ISSUE

8

8

REPLACES

RELEASE NO. PR-6074

CHECK

REVISIONS

A PR-6074

R E R

6 AUG 76

B C055729

K E W

29 AUG 84

C CO

56987

SMA

1 OCT 85

D CO

72387

WJC

27 JUN 92

E C076103

L F

4 OCT 93

CHECK

18 JUL 74

18 JUL 74

18 JUL 74

18 JUL 74

18 JUL 74




18 JUL 74

18 JUL 74

FO-52851

DRAWN

CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL
OPERATING FORCE----- 150 GRAM MAX	CONTACT ARRANGEMENT	DO NOT SCALE PRINT
RELEASE TRAVEL----- .010 MIN	S P D T	UNLESS OTHERWISE NOTED
RELEASE FORCE----- 15 GRAM MIN		DIMENSIONS ARE IN INCHES
		TOLERANCES ARE:
DIFFERENTIAL TRAVEL----- 0.05_0.26		ONE PLACE (.01) ±0.8/030
OVERTRAVEL----- 1.27 / .050 MIN		TWO PLACE (.001) ±0.38/015
FREE POSITION----- 15.88 / .625 MAX		THREE PLACE (.0001) ±0.15/005
		ANGLES ±
		WEIGHT .016 LB



- NOTES
- 1 - LINEAR MEASURE $\frac{\text{mm}}{\text{IN.}}$, mm/IN.
 - 2 - mm DIMENSIONS ARE FOR REF ONLY
 - 3 - TERMINALS ARE SILVER PLATED FOR SOLDERING

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[V3-3019](#)