




Agilent Sun Power Series HLMP-CB15, HLMP-CM15, HLMP-CB30, HLMP-CM30 T-1³/₄ (5 mm) Precision Optical Performance Best Value InGaN Blue and Green Lamps Data Sheet



Description

These high intensity blue and green LEDs are based on InGaN material technology. InGaN is the most efficient and cost effective material for LEDs in the blue and green region of the spectrum. The 472 nm typical dominant wavelength for blue and 526 nm typical dominant wavelength for green are well suited to color mixing in full color signs.

These LED lamps are untinted, nondiffused, T-1³/₄ packages incorporating second generation optics producing well defined spatial radiation patterns at specific viewing cone angles.

These lamps are made with an advanced optical grade epoxy, offering superior high temperature and high moisture resistance performance in outdoor signal and sign applications. The high maximum LED junction temperature limit of +130°C enables high temperature operation in bright sunlight conditions. The package epoxy contains both UV-A and UV-B inhibitors to reduce the effects of long term exposure to direct sunlight.

These lamps are available in two viewing angle options to give the designer flexibility with optical design.

Features

- Well defined spatial radiation pattern
- Viewing angles: 15° and 30°
- High luminous output
- Colors: 472 nm Blue, 526 nm Green
- Superior resistance to moisture
- UV resistant epoxy

Benefits

- Superior performance in outdoor environments
- Wavelengths suitable for color mixing in full color (RGB) signs

Applications

- Commercial outdoor signs
- Automotive interior lights
- Front panel indicators
- Front panel backlighting

CAUTION: HLMP-CBxx and HLMP-CMxx LEDs are Class 1 ESD sensitive. Please observe appropriate precautions during handling and processing. Refer to Agilent Application Note AN-1142 for additional details.



Agilent Technologies

LED Indicators

Device Selection Guide

Part Number	Typical Viewing Angle	Color and Dominant Wavelength λ_d (nm) Typ.	Luminous Intensity, I_v (mcd) Min.	Leads with Stand-Offs
HLMP-CB15-P0000	15°	Blue 472	765	No
HLMP-CB15-R0000	15°	Blue 472	1300	No
HLMP-CB30-K0000	30°	Blue 472	270	No
HLMP-CB30-M0000	30°	Blue 472	450	No
HLMP-CM15-S0000	15°	Green 526	1650	No
HLMP-CM15-W0000	15°	Green 526	4700	No
HLMP-CM30-M0000	30°	Green 526	450	No
HLMP-CM30-S0000	30°	Green 526	1650	No


Absolute Maximum Ratings at $T_A = 25^\circ\text{C}$

Parameter	Blue and Green
DC Forward Current ^[1]	30 mA
Peak Pulsed Forward Current	100 mA
Average Forward Current	30 mA
Reverse Voltage ($I_R = 100\ \mu\text{A}$)	5 V
Power Dissipation	120 mW
LED Junction Temperature	130°C
Operating Temperature Range	-40°C to +80°C
Storage Temperature Range	-40°C to +100°C
Soldering Temperature	260°C for 5 seconds

Note:

1. Derate linearly as shown in Figure 5 for temperatures above 50°C.

Package Dimensions



NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS (INCHES).

Electrical/Optical Characteristics at $T_A = 25^\circ\text{C}$

Parameter	Symbol	Min.	Typ.	Max.	Units	Test Conditions
Forward Voltage						
HLMP-CB15-P0000	V_F		3.8	4.0	V	$I_F = 20$ mA
HLMP-CB15-R0000			3.5	4.0		
HLMP-CB30-K0000			3.8	4.0		
HLMP-CB30-M0000			3.8	4.0		
HLMP-CM15-S0000			3.8	4.0		
HLMP-CM15-W0000			3.5	4.0		
HLMP-CM30-M0000			3.8	4.0		
HLMP-CM30-S0000			3.5	4.0		
Reverse Voltage	V_R	5				$I_R = 100$ μ A
Peak Wavelength						
Blue ($\lambda_d = 472$ nm)	λ_{peak}		470		nm	Peak of Wavelength of Spectral Distribution at $I_F = 20$ mA
Green ($\lambda_d = 526$ nm)			524			
Spectral Halfwidth						
Blue ($\lambda_d = 472$ nm)	$\Delta\lambda_{1/2}$		35		nm	Wavelength Width at Spectral Power Point at $I_F = 20$ mA
Green ($\lambda_d = 526$ nm)			47			
Capacitance	C		43		pF	$V_F = 0$, $F = 1$ MHz
Luminous Efficacy						
Blue ($\lambda_d = 472$ nm)	η_v		75		lm/W	Emitted Luminous Power/Emitted Radiant Power
Green ($\lambda_d = 526$ nm)			520			
Thermal Resistance	$R_{\Theta J-PIN}$		240		$^\circ\text{C/W}$	LED Junction-to-Cathode Lead




Figure 1. Relative intensity vs. wavelength.




Figure 2. Forward current vs. forward voltage (for HLMP-CB15-R0000, HLMP-CM15-W0000 and HLMP-CM30-S0000).




Figure 3. Forward current vs. forward voltage (for HLMP-CB15-P0000, HLMP-CB30-K0000, HLMP-CB30-M0000, HLMP-CM15-S0000 and HLMP-CM30-M0000).




Figure 4. Relative luminous intensity vs. forward current.




Figure 5. Maximum forward current vs. ambient temperature.




Figure 6. Spatial radiation pattern – 15° lamps.




Figure 7. Spatial radiation pattern – 30° lamps.




Figure 8. Color vs. forward current.




Figure 9. Normalized I_v vs. T (green).

Color Bin Limits (nm at 20 mA)

Blue	Color Range (nm)	
Bin ID	Min.	Max.
1	460.0	464.0
2	464.0	468.0
3	468.0	472.0
4	472.0	476.0
5	476.0	480.0

Tolerance for each bin limit is ± 2 nm.

Green	Color Range (nm)	
Bin ID	Min.	Max.
3	520.0	525.0
4	525.0	530.0
5	530.0	535.0
6	535.0	540.0

Tolerance for each bin limit is ± 2 nm.

Intensity Bin Limits

Bin Name	Min.	Max.
K	310	400
L	400	520
M	520	680
N	680	880
P	880	1150
Q	1150	1500
R	1500	1900
S	1900	2500
T	2500	3200
U	3200	4200
V	4200	5500
W	5500	7200

Tolerance of each minimum and maximum is $\pm 15\%$.

Note:

1. All bin categories are established for classification of products. Products may not be available in all bin categories. Please contact your Agilent representatives for further information.

www.agilent.com/semiconductors

For product information and a complete list of distributors, please go to our web site.

For technical assistance call:

Americas/Canada: +1 (800) 235-0312 or (408) 654-8675

Europe: +49 (0) 6441 92460

China: 10800 650 0017

Hong Kong: (+65) 271 2451

India, Australia, New Zealand: (+65) 271 2394

Japan: (+81 3) 3335-8152(Domestic/International), or 0120-61-1280(Domestic Only)

Korea: (+65) 271 2194

Malaysia, Singapore: (+65) 271 2054

Taiwan: (+65) 271 2654

Data subject to change.

Copyright © 2002 Agilent Technologies, Inc.

Obsoletes 5988-0334EN

March 27, 2002

5988-5676EN



Agilent Technologies