









Copyright FCI.

PART NUMBER SEE SHEET 2



spec ref *		dr Rainbow Zhan		2014/05/19		projection 	MM 	size A3	scale 3:2		
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng Rainbow Zhan	2015/01/07			ecn no -			
ASME Y14.5				chr -	-			rel level Released			
				appr Pei-Ming Zheng				2015/01/07		product family PwrBlade+	
surface  ASME Y14.5	linear	0.X	±0.5		title 3LP + 16S + 4LP VERTICAL PF HEADER			dwg no 10106267-0704001	rev A		
		0.XX	±0.25								
		0.XXX	±0.10								
ASME Y14.5	angular	0°	±2°	www.fci.com	cat. no.		Product - Customer Drw			sheet 1 of 3	

A

B

C

D


A

B

C

D

- NOTES:
- 1) "FCI", PART NUMBER AND DATE CODE TO BE MARKED ON THIS SURFACE.
THE MARK CAN BE OMITTED IF THERE IS NOT ENOUGH SPACE ON THIS SURFACE.
- 2) MATERIALS:
-HOUSING - GLASS FILLED WITH HIGH TEMP THERMOPLASTIC, UL94V-0.
-SIGNAL CONTACT - COPPER ALLOY.
-POWER CONTACT - HIGH CONDUCTIVITY COPPER ALLOY.
- 3) PLATING SPECIFICATION REFER TO FCI 10116351
- 4) DENOTES CONNECTOR KEEP OUT ZONE.
- 5) DATUM AND BASIC DIMENIONS WERE ESTABLISHED BY CUSTOMER.
- 6) ALL HOLE DIAMETERS ARE FINISHED HOLE SIZES.
- 7) 1.15±0.025MM DRILLED HOLE PLATED WITH 0.00762MM MIN Sn
OVER 0.0254-0.0762MM Cu PLATING TO ACHIEVE A 1.02±0.07MM HOLE.
- 8) PRODUCT SPECIFICATION REFER TO FCI GS-12-658.
APPLICATION SPECIFICATION REFER TO FCI GS-20-141.
PRODUCT PACKAGED IN TRAYS, REFER TO FCI GS-14-1502.



dr	Rainbow Zhan	2014/05/19	projection	MM	size	scale
eng	Rainbow Zhan	2015/01/07			A3	3:2
chr	-	-			ecn no	-
appr	Pei-Ming Zheng	2015/01/07	product family	PwrBlade+	rel level	Released
FCI www.fci.com		3LP + 16S + 4LP VERTICAL PF HEADER			dwg no	rev
					10106267-0704001	A
cat. no.			Product - Customer Drw			sheet 3 of 3